

PT Select



PT SELECT BEARING INTERCHANGE GUIDE



RegalRexnord™

FEATURES & BENEFITS

Specialized geometry and materials that run cooler, vibrate less, and support heavier loads with a lighter housing

Drop-in replacement saves installation time and money

QR code connects to installation, maintenance, technical, born on info plus one year extended warranty

Triple lip seal provides best-in-class ingress protection and speed ratings for a wide variety of applications. Clearance seals also available

100% spin testing to ensure smooth concentric load distribution

Additional Features & Benefits

- State-of-the-art housing design allows increased strength while optimizing material
- Industry-standard dimensions for interchangeability with leading brands
- Standard, off-the-shelf sizes for quick turnaround needs
- Rugged metal retainer for increased strength and durability
- Shaft ready and pre-lubricated with our standard grease for normal operation

BEARING HOUSING STYLE OPTIONS



2-bolt Pillow Block

- Bore range: 1-7/16 – 3-15/16 in
- Optional clearance seal
- Expansion unit available



4-bolt Pillow Block

- Bore range: 1-15/16 – 4-7/16 in
- Optional clearance seal
- Expansion unit available
- 4-bolt Pillow Block – Type E available for 3-1/2 in bore size



2-bolt Pillow Block – Type E

- Bore range: 1-7/16 – 3-7/16 in
- Optional clearance seal
- Expansion unit available



Flange Block

- Bore range: 1-7/16 – 3-15/16 in
- Optional clearance seal
- Expansion unit available



Flange Block – Type E

- Bore range: 1-7/16 – 3-15/16 in
- Optional clearance seal
- Expansion unit available



Piloted Flange

- Bore range: 1-7/16 – 4-7/16 in
- Optional clearance seal
- Expansion unit available



PT Select Housing — Type E Flanged Unit; 4 Bolt Square

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/ Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-QM**	Hub City**	FYH**	Jones	Moline**	PTI**
1-7/16	Clearance Seal	Fixed	EFB107C	EF4BS2-107L	071496	FYE1716H18	NONE	QAF08A-107ST	KFBE-1716LT	XSE4F408-23L	NONE	292-11-107L	NONE
1-7/16	Clearance Seal	Expansion	EFB107CE	EF4BS2-107LE	071509	FYE171618	NONE	QAF08A-107SET	NONE	XSE4F408-23FL	NONE	291-11-107L	NONE
1-7/16	Triple Lip Seal	Fixed	EFB107T	EF4BS2-107R	071470	FYE1716H	NONE	QAF08A-107SM	KFBE-1716DN	XSE4F408-23	NONE	292-11-107	NONE
1-7/16	Triple Lip Seal	Expansion	EFB107TE	EF4BS2-107RE	071483	FYE1716	NONE	QAF08A-107SEM	NONE	XSE4F408-23F	NONE	291-11-107	NONE
1-11/16	Clearance Seal	Fixed	EFB111C	EF4BS2-111L	071497	FYE11116H18	NONE	QAF09A-111ST	KFBE-11116LT	XSE4F409-27L	NONE	292-11-111L	NONE
1-11/16	Clearance Seal	Expansion	EFB111CE	EF4BS2-111LE	071510	FYE1111618	NONE	QAF09A-111SET	NONE	XSE4F409-27FL	NONE	291-11-111L	NONE
1-11/16	Triple Lip Seal	Fixed	EFB111T	EF4BS2-111R	071471	FYE11116H	NONE	QAF09A-111SM	KFBE-11116DN	XSE4F409-27	NONE	292-11-111	NONE
1-11/16	Triple Lip Seal	Expansion	EFB111TE	EF4BS2-111RE	071484	FYE11116	NONE	QAF09A-111SEM	NONE	XSE4F409-27F	NONE	291-11-111	NONE
1-15/16	Clearance Seal	Fixed	EFB115C	EF4BS2-115L	071498	FYE11516H18	USFBE5000-115	QAF10A-115ST	KFBE-11516LT	XSE4F410-31L	NONE	292-11-115L	NONE
1-15/16	Clearance Seal	Expansion	EFB115CE	EF4BS2-115LE	071511	FYE1151618	USFBE5000E-115	QAF10A-115SET	NONE	XSE4F410-31FL	NONE	291-11-115L	NONE
1-15/16	Triple Lip Seal	Fixed	EFB115T	EF4BS2-115R	071472	FYE11516H	USFBE5000-115C	QAF10A-115SM	KFBE-11516DN	XSE4F410-31	NONE	292-11-115	NONE
1-15/16	Triple Lip Seal	Expansion	EFB115TE	EF4BS2-115RE	071485	FYE11516	USFBE5000E-115C	QAF10A-115SEM	NONE	XSE4F410-31F	NONE	291-11-115	NONE
2-3/16	Clearance Seal	Fixed	EFB203C	EF4BS2-203L	071500	FYE2316H18	USFBE5000-203	QAF11A-203ST	KFBE-2316LT	XSE4F411-35L	NONE	292-11-203L	NONE
2-3/16	Clearance Seal	Expansion	EFB203CE	EF4BS2-203LE	071513	FYE231618	USFBE5000E-203	QAF11A-203SET	NONE	XSE4F411-35FL	NONE	291-11-203L	NONE
2-3/16	Triple Lip Seal	Fixed	EFB203T	EF4BS2-203R	071474	FYE2316H	USFBE5000-203C	QAF11A-203SM	KFBE-2316DN	XSE4F411-35	NONE	292-11-203	NONE
2-3/16	Triple Lip Seal	Expansion	EFB203TE	EF4BS2-203RE	071487	FYE2316	USFBE5000E-203C	QAF11A-203SEM	NONE	XSE4F411-35F	NONE	291-11-203	NONE
2-7/16	Clearance Seal	Fixed	EFB207C	EF4BS2-207L	071501	FYE2716H18	USFBE5000-207	QAF13A-207ST	KFBE-2716LT	XSE4F413-39L	NONE	292-11-207L	NONE
2-7/16	Clearance Seal	Expansion	EFB207CE	EF4BS2-207LE	071514	FYE271618	USFBE5000E-207	QAF13A-207SET	NONE	XSE4F413-39FL	NONE	291-11-207L	NONE
2-7/16	Triple Lip Seal	Fixed	EFB207T	EF4BS2-207R	071475	FYE2716H	USFBE5000-207C	QAF13A-207SM	KFBE-2716DN	XSE4F413-39	NONE	292-11-207	NONE
2-7/16	Triple Lip Seal	Expansion	EFB207TE	EF4BS2-207RE	071488	FYE2716	USFBE5000E-207C	QAF13A-207SEM	NONE	XSE4F413-39F	NONE	291-11-207	NONE
2-1/2	Clearance Seal	Fixed	EFB208C	NONE	NONE	FYE212H18	USFBE5000-208	QAF13A-208ST	KFBE-212LT	XSE4F413-40L	NONE	292-11-208L	NONE
2-1/2	Clearance Seal	Expansion	EFB208CE	NONE	NONE	FYE21218	USFBE5000E-208	QAF13A-208SET	NONE	XSE4F413-40FL	NONE	291-11-208L	NONE
2-1/2	Triple Lip Seal	Fixed	EFB208T	NONE	NONE	FYE212H	USFBE5000-208C	QAF13A-208SM	KFBE-212DN	XSE4F413-40	NONE	292-11-208	NONE
2-1/2	Triple Lip Seal	Expansion	EFB208TE	NONE	NONE	FYE212	USFBE5000E-208C	QAF13A-208SEM	NONE	XSE4F413-40F	NONE	291-11-208	NONE
2-11/16	Clearance Seal	Fixed	EFB211C	EF4BS2-211L	071502	FYE21116H18	USFBE5000-211	QAF15A-211ST	KFBE-21116LT	XSE4F415-43L	NONE	292-11-211L	NONE
2-11/16	Clearance Seal	Expansion	EFB211CE	EF4BS2-211LE	071515	FYE2111618	USFBE5000E-211	QAF15A-211SET	NONE	XSE4F415-43FL	NONE	291-11-211L	NONE
2-11/16	Triple Lip Seal	Fixed	EFB211T	EF4BS2-211R	071476	FYE21116H	USFBE5000-211C	QAF15A-211SM	KFBE-21116DN	XSE4F415-43	NONE	292-11-211	NONE
2-11/16	Triple Lip Seal	Expansion	EFB211TE	EF4BS2-211RE	071489	FYE21116	USFBE5000E-211C	QAF15A-211SEM	NONE	XSE4F415-43F	NONE	291-11-211	NONE
2-15/16	Clearance Seal	Fixed	EFB215C	EF4BS2-215L	071503	FYE21516H18	USFBE5000-215	QAF15A-215ST	KFBE-21516LT	XSE4F415-47L	NONE	292-11-215L	NONE
2-15/16	Clearance Seal	Expansion	EFB215CE	EF4BS2-215LE	071516	FYE2151618	USFBE5000E-215	QAF15A-215SET	NONE	XSE4F415-47FL	NONE	291-11-215L	NONE
2-15/16	Triple Lip Seal	Fixed	EFB215T	EF4BS2-215R	071477	FYE21516H	USFBE5000-215C	QAF15A-215SM	KFBE-21516DN	XSE4F415-47	NONE	292-11-215	NONE
2-15/16	Triple Lip Seal	Expansion	EFB215TE	EF4BS2-215RE	071490	FYE21516	USFBE5000E-215C	QAF15A-215SEM	NONE	XSE4F415-47F	NONE	291-11-215	NONE
3-7/16	Clearance Seal	Fixed	EFB307C	EF4BS2-307L	071505	FYE3716H18	USFBE5000-307	QAF18A-307ST	KFBE-3716LT	XSE4F418-55L	NONE	292-11-307L	NONE
3-7/16	Clearance Seal	Expansion	EFB307CE	EF4BS2-307LE	071518	FYE371618	USFBE5000E-307	QAF18A-307SET	NONE	XSE4F418-55FL	NONE	291-11-307L	NONE
3-7/16	Triple Lip Seal	Fixed	EFB307T	EF4BS2-307R	071479	FYE3716H	USFBE5000-307C	QAF18A-307SM	KFBE-3716DN	XSE4F418-55	NONE	292-11-307	NONE
3-7/16	Triple Lip Seal	Expansion	EFB307TE	EF4BS2-307RE	071492	FYE3716	USFBE5000E-307C	QAF18A-307SEM	NONE	XSE4F418-55F	NONE	291-11-307	NONE
3-1/2	Clearance Seal	Fixed	EFB308C	NONE	NONE	FYE312H18	USFBE5000-308	QAF18A-308ST	KFBE-312LT	XSE4F418-56L	NONE	292-11-308L	NONE
3-1/2	Clearance Seal	Expansion	EFB308CE	NONE	NONE	FYE31218	USFBE5000E-308	QAF18A-308SET	NONE	XSE4F418-56FL	NONE	291-11-308L	NONE
3-1/2	Triple Lip Seal	Fixed	EFB308T	NONE	NONE	FYE312H	USFBE5000-308C	QAF18A-308SM	KFBE-312DN	XSE4F418-56	NONE	292-11-308	NONE
3-1/2	Triple Lip Seal	Expansion	EFB308TE	NONE	NONE	FYE312	USFBE5000E-308C	QAF18A-308SEM	NONE	XSE4F418-56F	NONE	291-11-308	NONE
3-15/16	Clearance Seal	Fixed	EFB315C	EF4BS2-315L	071506	FYE31516H18	USFBE5000-315	QAF20A-315ST	KFBE-31516LT	XSE4F420-63L	NONE	292-11-315L	NONE
3-15/16	Clearance Seal	Expansion	EFB315CE	EF4BS2-315LE	071519	FYE3151618	USFBE5000E-315	QAF20A-315SET	NONE	XSE4F420-63FL	NONE	291-11-315L	NONE
3-15/16	Triple Lip Seal	Fixed	EFB315T	EF4BS2-315R	071480	FYE31516H	USFBE5000-315C	QAF20A-315SM	KFBE-31516DN	XSE4F420-63	NONE	292-11-315	NONE
3-15/16	Triple Lip Seal	Expansion	EFB315TE	EF4BS2-315RE	071493	FYE31516	USFBE5000E-315C	QAF20A-315SEM	NONE	XSE4F420-63F	NONE	291-11-315	NONE

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.



PT Select Housing — Flanged Unit; 4 Bolt Square

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/ Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-QM**	Hub City**	FYH**	Jones	Moline**	PTI**
1-7/16	Clearance Seal	Fixed	FB107C	F4SS2-107L	070601	FYR1716H18	USFB5000-107	QAFL08A-107ST	KFB-1716LT	XS4F408-23L	NONE	192-11-107L	SR2FB4-107SLNE
1-7/16	Clearance Seal	Expansion	FB107CE	F4SS2-107LE	070854	FYR171618	USFB5000E-107	QAFL08A-107SET	NONE	XS4F408-23FL	NONE	191-11-107L	SR2FB4-107SLXP
1-7/16	Triple Lip Seal	Fixed	FB107T	F4BUN2-107	048034	FYR1716H	USFB5000-107C	QAFL08A-107SM	KFB-1716DN	XS4F408-23	NONE	192-11-107	SR2FB4-107R3NE
1-7/16	Triple Lip Seal	Expansion	FB107TE	F4BUN2-107E	048051	FYR1716	USFB5000E-107C	QAFL08A-107SEM	NONE	XS4F408-23F	NONE	191-11-107	SR2FB4-107R3XP
1-11/16	Clearance Seal	Fixed	FB111C	F4SS2-111L	070604	FYR11116H18	USFB5000-111	QAFL09A-111ST	KFB-11116LT	XS4F409-27L	NONE	192-11-111L	SR2FB4-111SLNE
1-11/16	Clearance Seal	Expansion	FB111CE	F4SS2-111LE	070857	FYR1111618	USFB5000E-111	QAFL09A-111SET	NONE	XS4F409-27FL	NONE	191-11-111L	SR2FB4-111SLXP
1-11/16	Triple Lip Seal	Fixed	FB111T	F4BUN2-111	048036	FYR11116H	USFB5000-111C	QAFL09A-111SM	KFB-11116DN	XS4F409-27	JYR2111	192-11-111	SR2FB4-111R3NE
1-11/16	Triple Lip Seal	Expansion	FB111TE	F4BUN2-111E	048053	FYR11116	USFB5000E-111C	QAFL09A-111SEM	NONE	XS4F409-27F	JYR2111EXP	191-11-111	SR2FB4-111R3XP
1-15/16	Clearance Seal	Fixed	FB115C	F4SS2-115L	070606	FYR11516H18	USFB5000-115	QAFL10A-115ST	KFB-11516LT	XS4F410-31L	NONE	192-11-115L	SR2FB4-115SLNE
1-15/16	Clearance Seal	Expansion	FB115CE	F4SS2-115LE	070859	FYR1151618	USFB5000E-115	QAFL10A-115SET	NONE	XS4F410-31FL	NONE	191-11-115L	SR2FB4-115SLXP
1-15/16	Triple Lip Seal	Fixed	FB115T	F4BUN2-115	048038	FYR11516H	USFB5000-115C	QAFL10A-115SM	KFB-11516DN	XS4F410-31	JYR2115	192-11-115	SR2FB4-115R3NE
1-15/16	Triple Lip Seal	Expansion	FB115TE	F4BUN2-115E	048055	FYR11516	USFB5000E-115C	QAFL10A-115SEM	NONE	XS4F410-31F	JYR2115EXP	191-11-115	SR2FB4-115R3XP
2-3/16	Clearance Seal	Fixed	FB203C	F4SS2-203L	070608	FYR2316H18	USFB5000-203	QAFL11A-203ST	KFB-2316LT	XS4F411-35L	NONE	192-11-203L	SR2FB4-203SLNE
2-3/16	Clearance Seal	Expansion	FB203CE	F4SS2-203LE	070861	FYR231618	USFB5000E-203	QAFL11A-203SET	NONE	XS4F411-35FL	NONE	191-11-203L	SR2FB4-203SLXP
2-3/16	Triple Lip Seal	Fixed	FB203T	F4BUN2-203	048040	FYR2316H	USFB5000-203C	QAFL11A-203SM	KFB-2316DN	XS4F411-35	JYR2203	192-11-203	SR2FB4-203R3NE
2-3/16	Triple Lip Seal	Expansion	FB203TE	F4BUN2-203E	048057	FYR2316	USFB5000E-203C	QAFL11A-203SEM	NONE	XS4F411-35F	JYR2203EXP	191-11-203	SR2FB4-203R3XP
2-7/16	Clearance Seal	Fixed	FB207C	F4SS2-207L	070610	FYR2716H18	USFB5000-207	QAFL13A-207ST	KFB-2716LT	XS4F413-39L	NONE	192-11-207L	SR2FB4-207SLNE
2-7/16	Clearance Seal	Expansion	FB207CE	F4SS2-207LE	070863	FYR271618	USFB5000E-207	QAFL13A-207SET	NONE	XS4F413-39FL	NONE	191-11-207L	SR2FB4-207SLXP
2-7/16	Triple Lip Seal	Fixed	FB207T	F4BUN2-207	048041	FYR2716H	USFB5000-207C	QAFL13A-207SM	KFB-2716DN	XS4F413-39	JYR2207	192-11-207	SR2FB4-207R3NE
2-7/16	Triple Lip Seal	Expansion	FB207TE	F4BUN2-207E	048058	FYR2716	USFB5000E-207C	QAFL13A-207SEM	NONE	XS4F413-39F	JYR2207EXP	191-11-207	SR2FB4-207R3XP
2-1/2	Clearance Seal	Fixed	FB208C	NONE	NONE	FYR212H18	USFB5000-208	QAFL13A-208ST	KFB-212LT	XS4F413-40L	NONE	192-11-208L	SR2FB4-208SLNE
2-1/2	Clearance Seal	Expansion	FB208CE	NONE	NONE	FYR21218	USFB5000E-208	QAFL13A-208SET	NONE	XS4F413-40FL	NONE	191-11-208L	SR2FB4-208SLXP
2-1/2	Triple Lip Seal	Fixed	FB208T	F4BUN2-208	048042	FYR212H	USFB5000-208C	QAFL13A-208SM	KFB-212DN	XS4F413-40	JYR2208	192-11-208	SR2FB4-208R3NE
2-1/2	Triple Lip Seal	Expansion	FB208TE	F4BUN2-208E	048059	FYR212	USFB5000E-208C	QAFL13A-208SEM	NONE	XS4F413-40F	JYR2208EXP	191-11-208	SR2FB4-208R3XP
2-11/16	Clearance Seal	Fixed	FB211C	F4SS2-211L	070612	FYR21116H18	USFB5000-211	QAFL15A-211ST	KFB-21116LT	XS4F415-43L	NONE	192-11-211L	SR2FB4-211SLNE
2-11/16	Clearance Seal	Expansion	FB211CE	F4SS2-211LE	070865	FYR2111618	USFB5000E-211	QAFL15A-211SET	NONE	XS4F415-43FL	NONE	191-11-211L	SR2FB4-211SLXP
2-11/16	Triple Lip Seal	Fixed	FB211T	F4BUN2-211	048043	FYR21116H	USFB5000-211C	QAFL15A-211SM	KFB-21116DN	XS4F415-43	JYR2211	192-11-211	SR2FB4-211R3NE
2-11/16	Triple Lip Seal	Expansion	FB211TE	F4BUN2-211E	048060	FYR21116	USFB5000E-211C	QAFL15A-211SEM	NONE	XS4F415-43F	JYR2211EXP	191-11-211	SR2FB4-211R3XP
2-15/16	Clearance Seal	Fixed	FB215C	F4SS2-215L	070613	FYR21516H18	USFB5000-215	QAFL15A-215ST	KFB-21516LT	XS4F415-47L	NONE	192-11-215L	SR2FB4-215SLNE
2-15/16	Clearance Seal	Expansion	FB215CE	F4SS2-215LE	070866	FYR2151618	USFB5000E-215	QAFL15A-215SET	NONE	XS4F415-47FL	NONE	191-11-215L	SR2FB4-215SLXP
2-15/16	Triple Lip Seal	Fixed	FB215T	F4BUN2-215	048045	FYR21516H	USFB5000-215C	QAFL15A-215SM	KFB-21516DN	XS4F415-47	JYR2215	192-11-215	SR2FB4-215R3NE
2-15/16	Triple Lip Seal	Expansion	FB215TE	F4BUN2-215E	048062	FYR21516	USFB5000E-215C	QAFL15A-215SEM	NONE	XS4F415-47F	JYR2215EXP	191-11-215	SR2FB4-215R3XP
3-7/16	Clearance Seal	Fixed	FB307C	F4SS2-307L	070616	FYR3716H18	USFB5000-307	QAFL18A-307ST	KFB-3716LT	XS4F418-55L	NONE	192-11-307L	SR2FB4-307SLNE
3-7/16	Clearance Seal	Expansion	FB307CE	F4SS2-307LE	070869	FYR371618	USFB5000E-307	QAFL18A-307SET	NONE	XS4F418-55FL	NONE	191-11-307L	SR2FB4-307SLXP
3-7/16	Triple Lip Seal	Fixed	FB307T	F4BUN2-307	048047	FYR3716H	USFB5000-307C	QAFL18A-307SM	KFB-3716DN	XS4F418-55	JYR2307	192-11-307	SR2FB4-307R3NE
3-7/16	Triple Lip Seal	Expansion	FB307TE	F4BUN2-307E	048064	FYR3716	USFB5000E-307C	QAFL18A-307SEM	NONE	XS4F418-55F	JYR2307EXP	191-11-307	SR2FB4-307R3XP
3-1/2	Clearance Seal	Fixed	FB308C	NONE	NONE	FYR312H18	USFB5000-308	QAFL18A-308ST	KFB-312LT	XS4F418-56L	NONE	192-11-308L	SR2FB4-308SLNE
3-1/2	Clearance Seal	Expansion	FB308CE	NONE	NONE	FYR31218	USFB5000E-308	QAFL18A-308SET	NONE	XS4F418-56FL	NONE	191-11-308L	SR2FB4-308SLXP
3-1/2	Triple Lip Seal	Fixed	FB308T	F4BUN2-308	048048	FYR312H	USFB5000-308C	QAFL18A-308SM	KFB-312DN	XS4F418-56	JYR2308	192-11-308	SR2FB4-308R3NE
3-1/2	Triple Lip Seal	Expansion	FB308TE	F4BUN2-308E	048065	FYR312	USFB5000E-308C	QAFL18A-308SEM	NONE	XS4F418-56F	JYR2308EXP	191-11-308	SR2FB4-308R3XP
3-15/16	Clearance Seal	Fixed	FB315C	F4SS2-315L	070618	FYR315H18	USFB5000-315	QAFL20A-315ST	KFB-31516LT	XS4F420-63L	NONE	192-11-315L	SR2FB4-315SLNE
3-15/16	Clearance Seal	Expansion	FB315CE	F4SS2-315LE	070871	FYR31518	USFB5000E-315	QAFL20A-315SET	NONE	XS4F420-63FL	NONE	191-11-315L	SR2FB4-315SLXP
3-15/16	Triple Lip Seal	Fixed	FB315T	F4BUN2-315	048049	FYR315H	USFB5000-315C	QAFL20A-315SM	KFB-31516DN	XS4F420-63	JYR2315	192-11-315	SR2FB4-315R3NE
3-15/16	Triple Lip Seal	Expansion	FB315TE	F4BUN2-315E	048066	FYR315	USFB5000E-315C	QAFL20A-315SEM	NONE	XS4F420-63F	JYR2315EXP	191-11-315	SR2FB4-315R3XP

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.



Flanged Cartridge Unit; 4-Bolt Round

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-QM**	Hub City**	FYH**	Jones	Moline**	PTI**
1-7/16	Clearance Seal	Fixed	FC107C	FCS2-107L	070699	FYRP1716H18	USFC5000-107	QAC08A-107ST	NONE	XS4FC408-23L	NONE	192-31-107L	SR2FC-107SLNE
1-7/16	Clearance Seal	Expansion	FC107CE	FCS2-107LE	070726	FYRP1716H18	USFC5000E-107	QAC08A-107SET	NONE	XS4FC408-23FL	NONE	191-31-107L	SR2FC-107SLXP
1-7/16	Triple Lip Seal	Fixed	FC107T	FCS2-107R	070645	FYRP1716H	USFC5000-107C	QAC08A-107SM	NONE	XS4FC408-23	JYRP2107	192-31-107	SR2FC-107R3NE
1-7/16	Triple Lip Seal	Expansion	FC107TE	FCS2-107RE	070672	FYRP1716	USFC5000E-107C	QAC08A-107SEM	NONE	XS4FC408-23FL	JYRP2107EXP	191-31-107	SR2FC-107R3XP
1-11/16	Clearance Seal	Fixed	FC111C	FCS2-111L	070702	FYRP11116H18	USFC5000-111	QAC09A-111ST	NONE	XS4FC409-27L	NONE	192-31-111L	SR2FC-111SLNE
1-11/16	Clearance Seal	Expansion	FC111CE	FCS2-111LE	070729	FYRP11116H18	USFC5000E-111	QAC09A-111SET	NONE	XS4FC409-27FL	NONE	191-31-111L	SR2FC-111SLXP
1-11/16	Triple Lip Seal	Fixed	FC111T	FCS2-111R	070648	FYRP11116H	USFC5000-111C	QAC09A-111SM	NONE	XS4FC409-27	JYRP2111	192-31-111	SR2FC-111R3NE
1-11/16	Triple Lip Seal	Expansion	FC111TE	FCS2-111RE	070675	FYRP11116	USFC5000E-111C	QAC09A-111SEM	NONE	XS4FC409-27FL	JYRP2111EXP	191-31-111	SR2FC-111R3XP
1-15/16	Clearance Seal	Fixed	FC115C	FCS2-115L	070704	FYRP11516H18	USFC5000-115	QAC10A-115ST	NONE	XS4FC410-31L	NONE	192-31-115L	SR2FC-115SLNE
1-15/16	Clearance Seal	Expansion	FC115CE	FCS2-115LE	070731	FYRP11516H18	USFC5000E-115	QAC10A-115SET	NONE	XS4FC410-31FL	NONE	191-31-115L	SR2FC-115SLXP
1-15/16	Triple Lip Seal	Fixed	FC115T	FCS2-115R	070650	FYRP11516H	USFC5000-115C	QAC10A-115SM	NONE	XS4FC410-31	JYRP2115	192-31-115	SR2FC-115R3NE
1-15/16	Triple Lip Seal	Expansion	FC115TE	FCS2-115RE	070677	FYRP11516	USFC5000E-115C	QAC10A-115SEM	NONE	XS4FC410-31FL	JYRP2115EXP	191-31-115	SR2FC-115R3XP
2-3/16	Clearance Seal	Fixed	FC203C	FCS2-203L	070706	FYRP2316H18	USFC5000-203	QAC11A-203ST	NONE	XS4FC411-35L	NONE	192-31-203L	SR2FC-203SLNE
2-3/16	Clearance Seal	Expansion	FC203CE	FCS2-203LE	070733	FYRP2316H18	USFC5000E-203	QAC11A-203SET	NONE	XS4FC411-35FL	NONE	191-31-203L	SR2FC-203SLXP
2-3/16	Triple Lip Seal	Fixed	FC203T	FCS2-203R	070652	FYRP2316H	USFC5000-203C	QAC11A-203SM	NONE	XS4FC411-35	JYRP2203	192-31-203	SR2FC-203R3NE
2-3/16	Triple Lip Seal	Expansion	FC203TE	FCS2-203RE	070679	FYRP2316	USFC5000E-203C	QAC11A-203SEM	NONE	XS4FC411-35FL	JYRP2203EXP	191-31-203	SR2FC-203R3XP
2-7/16	Clearance Seal	Fixed	FC207C	FCS2-207L	070708	FYRP2716H18	USFC5000-207	QAC13A-207ST	NONE	XS4FC413-39L	NONE	192-31-207L	SR2FC-207SLNE
2-7/16	Clearance Seal	Expansion	FC207CE	FCS2-207LE	070735	FYRP2716H18	USFC5000E-207	QAC13A-207SET	NONE	XS4FC413-39FL	NONE	191-31-207L	SR2FC-207SLXP
2-7/16	Triple Lip Seal	Fixed	FC207T	FCS2-207R	070654	FYRP2716H	USFC5000-207C	QAC13A-207SM	NONE	XS4FC413-39	JYRP2207	192-31-207	SR2FC-207R3NE
2-7/16	Triple Lip Seal	Expansion	FC207TE	FCS2-207RE	070681	FYRP2716	USFC5000E-207C	QAC13A-207SEM	NONE	XS4FC413-39FL	JYRP2207EXP	191-31-207	SR2FC-207R3XP
2-1/2	Clearance Seal	Fixed	FC208C	NONE	NONE	FYRP212H18	USFC5000-208	QAC13A-208ST	NONE	XS4FC413-40L	NONE	192-31-208L	SR2FC-208SLNE
2-1/2	Clearance Seal	Expansion	FC208CE	NONE	NONE	FYRP212H18	USFC5000E-208	QAC13A-208SET	NONE	XS4FC413-40FL	NONE	191-31-208L	SR2FC-208SLXP
2-1/2	Triple Lip Seal	Fixed	FC208T	NONE	NONE	FYRP212H	USFC5000-208C	QAC13A-208SM	NONE	XS4FC413-40	JYRP2208	192-31-208	SR2FC-208R3NE
2-1/2	Triple Lip Seal	Expansion	FC208TE	NONE	NONE	FYRP212	USFC5000E-208C	QAC13A-208SEM	NONE	XS4FC413-40FL	JYRP2208EXP	191-31-208	SR2FC-208R3XP
2-11/16	Clearance Seal	Fixed	FC211C	FCS2-211L	070710	FYRP21116H18	USFC5000-211	QAC15A-211ST	NONE	XS4FC415-43L	NONE	192-31-211L	SR2FC-211SLNE
2-11/16	Clearance Seal	Expansion	FC211CE	FCS2-211LE	070737	FYRP21116H18	USFC5000E-211	QAC15A-211SET	NONE	XS4FC415-43FL	NONE	191-31-211L	SR2FC-211SLXP
2-11/16	Triple Lip Seal	Fixed	FC211T	FCS2-211R	070656	FYRP21116H	USFC5000-211C	QAC15A-211SM	NONE	XS4FC415-43	JYRP2211	192-31-211	SR2FC-211R3NE
2-11/16	Triple Lip Seal	Expansion	FC211TE	FCS2-211RE	070683	FYRP21116	USFC5000E-211C	QAC15A-211SEM	NONE	XS4FC415-43FL	JYRP2211EXP	191-31-211	SR2FC-211R3XP
2-15/16	Clearance Seal	Fixed	FC215C	FCS2-215L	070711	FYRP21516H18	USFC5000-215	QAC15A-215ST	NONE	XS4FC415-47L	NONE	192-31-215L	SR2FC-215SLNE
2-15/16	Clearance Seal	Expansion	FC215CE	FCS2-215LE	070738	FYRP21516H18	USFC5000E-215	QAC15A-215SET	NONE	XS4FC415-47FL	NONE	191-31-215L	SR2FC-215SLXP
2-15/16	Triple Lip Seal	Fixed	FC215T	FCS2-215R	070657	FYRP21516H	USFC5000-215C	QAC15A-215SM	NONE	XS4FC415-47	JYRP2215	192-31-215	SR2FC-215R3NE
2-15/16	Triple Lip Seal	Expansion	FC215TE	FCS2-215RE	070684	FYRP21516	USFC5000E-215C	QAC15A-215SEM	NONE	XS4FC415-47FL	JYRP2215EXP	191-31-215	SR2FC-215R3XP
3-7/16	Clearance Seal	Fixed	FC307C	FCS2-307L	070714	FYRP3716H18	USFC5000-307	QAC18A-307ST	NONE	XS4FC418-55L	NONE	192-31-307L	SR2FC-307SLNE
3-7/16	Clearance Seal	Expansion	FC307CE	FCS2-307LE	070741	FYRP3716H18	USFC5000E-307	QAC18A-307SET	NONE	XS4FC418-55FL	NONE	191-31-307L	SR2FC-307SLXP
3-7/16	Triple Lip Seal	Fixed	FC307T	FCS2-307R	070660	FYRP3716H	USFC5000-307C	QAC18A-307SM	NONE	XS4FC418-55	JYRP2307	192-31-307	SR2FC-307R3NE
3-7/16	Triple Lip Seal	Expansion	FC307TE	FCS2-307RE	070687	FYRP3716	USFC5000E-307C	QAC18A-307SEM	NONE	XS4FC418-55FL	JYRP2307EXP	191-31-307	SR2FC-307R3XP
3-1/2	Clearance Seal	Fixed	FC308C	NONE	NONE	FYRP312H18	USFC5000-308	QAC18A-308ST	NONE	XS4FC418-56L	NONE	192-31-308L	SR2FC-308SLNE
3-1/2	Clearance Seal	Expansion	FC308CE	NONE	NONE	FYRP312H18	USFC5000E-308	QAC18A-308SET	NONE	XS4FC418-56FL	NONE	191-31-308L	SR2FC-308SLXP
3-1/2	Triple Lip Seal	Fixed	FC308T	NONE	NONE	FYRP312H	USFC5000-308C	QAC18A-308SM	NONE	XS4FC418-56	JYRP2308	192-31-308	SR2FC-308R3NE
3-1/2	Triple Lip Seal	Expansion	FC308TE	NONE	NONE	FYRP312	USFC5000E-308C	QAC18A-308SEM	NONE	XS4FC418-56FL	JYRP2308EXP	191-31-308	SR2FC-308R3XP
3-15/16	Clearance Seal	Fixed	FC315C	FCS2-315L	070716	FYRP315H18	USFC5000-315	QAC20A-315ST	NONE	XS4FC420-63L	NONE	192-31-315L	SR2FC-315SLNE
3-15/16	Clearance Seal	Expansion	FC315CE	FCS2-315LE	070743	FYRP315H18	USFC5000E-315	QAC20A-315SET	NONE	XS4FC420-63FL	NONE	191-31-315L	SR2FC-315SLXP
3-15/16	Triple Lip Seal	Fixed	FC315T	FCS2-315R	070662	FYRP315H	USFC5000-315C	QAC20A-315SM	NONE	XS4FC420-63	JYRP2315	192-31-315	SR2FC-315R3NE
3-15/16	Triple Lip Seal	Expansion	FC315TE	FCS2-315RE	070689	FYRP315	USFC5000E-315C	QAC20A-315SEM	NONE	XS4FC420-63FL	JYRP2315EXP	191-31-315	SR2FC-315R3XP
4-7/16	Clearance Seal	Fixed	FC407C	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Clearance Seal	Expansion	FC407CE	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Triple Lip Seal	Fixed	FC407T	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Triple Lip Seal	Expansion	FC407TE	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.



PT Select Housing — Type E 2-Bolt Pillow Block

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/ Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-QM**	Hub City**	FYH**	Jones	Moline**	PTI**
1-7/16	Clearance Seal	Fixed	EP2B107C	EP2BS2-107L	071412	SYE1716H18	NONE	QAP08A-107ST	KPBE-1716LT	XSE2P408-23L	NONE	292-21-107L	SREPB2-107SLNE
1-7/16	Clearance Seal	Expansion	EP2B107CE	EP2BS2-107LE	071423	SYE171618	NONE	QAP08A-107SET	NONE	XSE2P408-23FL	NONE	291-21-107L	SREPB2-107SLXP
1-7/16	Triple Lip Seal	Fixed	EP2B107T	EP2BS2-107R	071390	SYE1716H	NONE	QAP08A-107SM	KPBE-1716DN	XSE2P408-23	JE2107	292-21-107	SREPB2-107R3NE
1-7/16	Triple Lip Seal	Expansion	EP2B107TE	EP2BS2-107RE	071401	SYE1716	NONE	QAP08A-107SEM	NONE	XSE2P408-23F	JE2107EXP	291-21-107	SREPB2-107R3XP
1-11/16	Clearance Seal	Fixed	EP2B111C	EP2BS2-111L	071413	SYE11116H18	NONE	QAP09A-111ST	KPBE-11116LT	XSE2P409-27L	NONE	292-21-111L	SREPB2-111SLNE
1-11/16	Clearance Seal	Expansion	EP2B111CE	EP2BS2-111LE	071424	SYE1111618	NONE	QAP09A-111SET	NONE	XSE2P409-27FL	NONE	291-21-111L	SREPB2-111SLXP
1-11/16	Triple Lip Seal	Fixed	EP2B111T	EP2BS2-111R	071391	SYE11116H	NONE	QAP09A-111SM	KPBE-11116DN	XSE2P409-27	JE2111	292-21-111	SREPB2-111R3NE
1-11/16	Triple Lip Seal	Expansion	EP2B111TE	EP2BS2-111RE	071402	SYE11116	NONE	QAP09A-111SEM	NONE	XSE2P409-27F	JE2111EXP	291-21-111	SREPB2-111R3XP
1-15/16	Clearance Seal	Fixed	EP2B115C	EP2BS2-115L	071414	SYE11516H18	USRBE5000-115	QAP10A-115ST	KPBE-11516LT	XSE2P410-31L	NONE	292-21-115L	SREPB2-115SLNE
1-15/16	Clearance Seal	Expansion	EP2B115CE	EP2BS2-115LE	071425	SYE1151618	USRBE5000E-115	QAP10A-115SET	NONE	XSE2P410-31FL	NONE	291-21-115L	SREPB2-115SLXP
1-15/16	Triple Lip Seal	Fixed	EP2B115T	EP2BS2-115R	071392	SYE11516H	USRBE5000-115C	QAP10A-115SM	KPBE-11516DN	XSE2P410-31	JE2115	292-21-115	SREPB2-115R3NE
1-15/16	Triple Lip Seal	Expansion	EP2B115TE	EP2BS2-115RE	071403	SYE11516	USRBE5000E-115C	QAP10A-115SEM	NONE	XSE2P410-31F	JE2115EXP	291-21-115	SREPB2-115R3XP
2-3/16	Clearance Seal	Fixed	EP2B203C	EP2BS2-203L	071416	SYE2316H18	USRBE5000-203	QAP11A-203ST	KPBE-2316LT	XSE2P411-35L	NONE	292-21-203L	SREPB2-203SLNE
2-3/16	Clearance Seal	Expansion	EP2B203CE	EP2BS2-203LE	071427	SYE231618	USRBE5000E-203	QAP11A-203SET	NONE	XSE2P411-35FL	NONE	291-21-203L	SREPB2-203SLXP
2-3/16	Triple Lip Seal	Fixed	EP2B203T	EP2BS2-203R	071394	SYE2316H	USRBE5000-203C	QAP11A-203SM	KPBE-2316DN	XSE2P411-35	JE2203	292-21-203	SREPB2-203R3NE
2-3/16	Triple Lip Seal	Expansion	EP2B203TE	EP2BS2-203RE	071405	SYE2316	USRBE5000E-203C	QAP11A-203SEM	NONE	XSE2P411-35F	JE2203EXP	291-21-203	SREPB2-203R3XP
2-7/16	Clearance Seal	Fixed	EP2B207C	EP2BS2-207L	071417	SYE2716H18	USRBE5000-207	QAP13A-207ST	KPBE-2716LT	XSE2P413-39L	NONE	292-21-207L	SREPB2-207SLNE
2-7/16	Clearance Seal	Expansion	EP2B207CE	EP2BS2-207LE	071428	SYE271618	USRBE5000E-207	QAP13A-207SET	NONE	XSE2P413-39FL	NONE	291-21-207L	SREPB2-207SLXP
2-7/16	Triple Lip Seal	Fixed	EP2B207T	EP2BS2-207R	071395	SYE2716H	USRBE5000-207C	QAP13A-207SM	KPBE-2716DN	XSE2P413-39	JE2207	292-21-207	SREPB2-207R3NE
2-7/16	Triple Lip Seal	Expansion	EP2B207TE	EP2BS2-207RE	071406	SYE2716	USRBE5000E-207C	QAP13A-207SEM	NONE	XSE2P413-39F	JE2207EXP	291-21-207	SREPB2-207R3XP
2-1/2	Clearance Seal	Fixed	EP2B208C	NONE	NONE	SYE212H18	USRBE5000-208	QAP13A-208ST	KPBE-212LT	XSE2P413-40L	NONE	292-21-208L	SREPB2-208SLNE
2-1/2	Clearance Seal	Expansion	EP2B208CE	NONE	NONE	SYE21218	USRBE5000E-208	QAP13A-208SET	NONE	XSE2P413-40FL	NONE	291-21-208L	SREPB2-208SLXP
2-1/2	Triple Lip Seal	Fixed	EP2B208T	NONE	NONE	SYE212H	USRBE5000-208C	QAP13A-208SM	KPBE-212DN	XSE2P413-40	JE2208	292-21-208	SREPB2-208R3NE
2-1/2	Triple Lip Seal	Expansion	EP2B208TE	NONE	NONE	SYE212	USRBE5000E-208C	QAP13A-208SEM	NONE	XSE2P413-40F	JE2208EXP	291-21-208	SREPB2-208R3XP
2-11/16	Clearance Seal	Fixed	EP2B211C	EP2BS2-211L	071418	SYE21116H18	USRBE5000-211	QAP15A-211ST	KPBE-21116LT	XSE2P415-43L	NONE	292-21-211L	SREPB2-211SLNE
2-11/16	Clearance Seal	Expansion	EP2B211CE	EP2BS2-211LE	071429	SYE2111618	USRBE5000E-211	QAP15A-211SET	NONE	XSE2P415-43FL	NONE	291-21-211L	SREPB2-211SLXP
2-11/16	Triple Lip Seal	Fixed	EP2B211T	EP2BS2-211R	071396	SYE21116H	USRBE5000-211C	QAP15A-211SM	KPBE-21116DN	XSE2P415-43	JE2211	292-21-211	SREPB2-211R3NE
2-11/16	Triple Lip Seal	Expansion	EP2B211TE	EP2BS2-211RE	071407	SYE21116	USRBE5000E-211C	QAP15A-211SEM	NONE	XSE2P415-43F	JE2211EXP	291-21-211	SREPB2-211R3XP
2-15/16	Clearance Seal	Fixed	EP2B215C	EP2BS2-215L	071419	SYE21516H18	USRBE5000-215	QAP15A-215ST	NONE	XSE2P415-47L	NONE	292-21-215L	SREPB2-215SLNE
2-15/16	Clearance Seal	Expansion	EP2B215CE	EP2BS2-215LE	071430	SYE2151618	USRBE5000E-215	QAP15A-215SET	NONE	XSE2P415-47FL	NONE	291-21-215L	SREPB2-215SLXP
2-15/16	Triple Lip Seal	Fixed	EP2B215T	EP2BS2-215R	071397	SYE21516H	USRBE5000-215C	QAP15A-215SM	NONE	XSE2P415-47	JE2215	292-21-215	SREPB2-215R3NE
2-15/16	Triple Lip Seal	Expansion	EP2B215TE	EP2BS2-215RE	071408	SYE21516	USRBE5000E-215C	QAP15A-215SEM	NONE	XSE2P415-47F	JE2215EXP	291-21-215	SREPB2-215R3XP
3-7/16	Clearance Seal	Fixed	EP2B307C	EP2BS2-307L	071421	SYE3716H18	USRBE5000-307	QAP18A-307ST	NONE	XSE2P418-55L	NONE	292-21-307L	SREPB2-307SLNE
3-7/16	Clearance Seal	Expansion	EP2B307CE	EP2BS2-307LE	071432	SYE371618	USRBE5000E-307	QAP18A-307SET	NONE	XSE2P418-55FL	NONE	291-21-307L	SREPB2-307SLXP
3-7/16	Triple Lip Seal	Fixed	EP2B307T	EP2BS2-307R	071399	SYE3716H	USRBE5000-307C	QAP18A-307SM	NONE	XSE2P418-55	JE2307	292-21-307	SREPB2-307R3NE
3-7/16	Triple Lip Seal	Expansion	EP2B307TE	EP2BS2-307RE	071410	SYE3716	USRBE5000E-307C	QAP18A-307SEM	NONE	XSE2P418-55F	JE2307EXP	291-21-307	SREPB2-307R3XP

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.



PT Select Housing — 2-Bolt Pillow Block

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/ Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-**	Hub City**	FYH**	Jones	Moline**	PTI**
1-7/16	Clearance Seal	Fixed	P2B107C	P2B52-107L	070319	SYR1716H18	USRB5000-107	QAPL08A-107ST	KPB-1716LT	XS2P408-23L	NONE	192-21-107L	SR2PB2-107SLNE
1-7/16	Clearance Seal	Expansion	P2B107CE	P2B52-107LE	070342	SYR171618	USRB5000E-107	QAPL08A-107SET	NONE	XS2P408-23FL	NONE	191-21-107L	SR2PB2-107SLXP
1-7/16	Triple Lip Seal	Fixed	P2B107T	P2B52-107R	070273	SYR1716H	USRB5000-107C	QAPL08A-107SM	KPB-1716DN	XS2P408-23	JA2107	192-21-107	SR2PB2-107R3NE
1-7/16	Triple Lip Seal	Expansion	P2B107TE	P2B52-107RE	070296	SYR1716	USRB5000E-107C	QAPL08A-107SEM	NONE	XS2P408-23F	JA2107EXP	191-21-107	SR2PB2-107R3XP
1-11/16	Clearance Seal	Fixed	P2B111C	P2B52-111L	070322	SYR11116H18	USRB5000-111	QAPL09A-111ST	KPB-11116LT	XS2P409-27L	NONE	192-21-111L	SR2PB2-111SLNE
1-11/16	Clearance Seal	Expansion	P2B111CE	P2B52-111LE	070345	SYR1111618	USRB5000E-111	QAPL09A-111SET	NONE	XS2P409-27FL	NONE	191-21-111L	SR2PB2-111SLXP
1-11/16	Triple Lip Seal	Fixed	P2B111T	P2B52-111R	070276	SYR11116H	USRB5000-111C	QAPL09A-111SM	KPB-11116DN	XS2P409-27	JA2111	192-21-111	SR2PB2-111R3NE
1-11/16	Triple Lip Seal	Expansion	P2B111TE	P2B52-111RE	070299	SYR11116	USRB5000E-111C	QAPL09A-111SEM	NONE	XS2P409-27F	JA2111EXP	191-21-111	SR2PB2-111R3XP
1-15/16	Clearance Seal	Fixed	P2B115C	P2B52-115L	070324	SYR11516H18	USRB5000-115	QAPL10A-115ST	KPB-11516LT	XS2P410-31L	NONE	192-21-115L	SR2PB2-115SLNE
1-15/16	Clearance Seal	Expansion	P2B115CE	P2B52-115LE	070347	SYR1151618	USRB5000E-115	QAPL10A-115SET	NONE	XS2P410-31FL	NONE	191-21-115L	SR2PB2-115SLXP
1-15/16	Triple Lip Seal	Fixed	P2B115T	P2B52-115R	070278	SYR11516H	USRB5000-115C	QAPL10A-115SM	KPB-11516DN	XS2P410-31	JA2115	192-21-115	SR2PB2-115R3NE
1-15/16	Triple Lip Seal	Expansion	P2B115TE	P2B52-115RE	070301	SYR11516	USRB5000E-115C	QAPL10A-115SEM	NONE	XS2P410-31F	JA2115EXP	191-21-115	SR2PB2-115R3XP
2-3/16	Clearance Seal	Fixed	P2B203C	P2B52-203L	070326	SYR2316H18	USRB5000-203	QAPL11A-203ST	KPB-2316LT	XS2P411-35L	NONE	192-21-203L	SR2PB2-203SLNE
2-3/16	Clearance Seal	Expansion	P2B203CE	P2B52-203LE	070349	SYR231618	USRB5000E-203	QAPL11A-203SET	NONE	XS2P411-35FL	NONE	191-21-203L	SR2PB2-203SLXP
2-3/16	Triple Lip Seal	Fixed	P2B203T	P2B52-203R	070280	SYR2316H	USRB5000-203C	QAPL11A-203SM	KPB-2316DN	XS2P411-35	JA2203	192-21-203	SR2PB2-203R3NE
2-3/16	Triple Lip Seal	Expansion	P2B203TE	P2B52-203RE	070303	SYR2316	USRB5000E-203C	QAPL11A-203SEM	NONE	XS2P411-35F	JA2203EXP	191-21-203	SR2PB2-203R3XP
2-7/16	Clearance Seal	Fixed	P2B207C	P2B52-207L	070328	SYR2716H18	USRB5000-207	QAPL13A-207ST	KPB-2716LT	XS2P413-39L	NONE	192-21-207L	SR2PB2-207SLNE
2-7/16	Clearance Seal	Expansion	P2B207CE	P2B52-207LE	070351	SYR271618	USRB5000E-207	QAPL13A-207SET	NONE	XS2P413-39FL	NONE	191-21-207L	SR2PB2-207SLXP
2-7/16	Triple Lip Seal	Fixed	P2B207T	P2B52-207R	070282	SYR2716H	USRB5000-207C	QAPL13A-207SM	KPB-2716DN	XS2P413-39	JA2207	192-21-207	SR2PB2-207R3NE
2-7/16	Triple Lip Seal	Expansion	P2B207TE	P2B52-207RE	070305	SYR2716	USRB5000E-207C	QAPL13A-207SEM	NONE	XS2P413-39F	JA2207EXP	191-21-207	SR2PB2-207R3XP
2-1/2	Clearance Seal	Fixed	P2B208C	NONE	NONE	SYR212H18	USRB5000-208	QAPL13A-208ST	KPB-212LT	XS2P413-40L	NONE	192-21-208L	SR2PB2-208SLNE
2-1/2	Clearance Seal	Expansion	P2B208CE	NONE	NONE	SYR21218	USRB5000E-208	QAPL13A-208SET	NONE	XS2P413-40FL	NONE	191-21-208L	SR2PB2-208SLXP
2-1/2	Triple Lip Seal	Fixed	P2B208T	NONE	NONE	SYR212H	USRB5000-208C	QAPL13A-208SM	KPB-212DN	XS2P413-40	JA2208	192-21-208	SR2PB2-208R3NE
2-1/2	Triple Lip Seal	Expansion	P2B208TE	NONE	NONE	SYR212	USRB5000E-208C	QAPL13A-208SEM	NONE	XS2P413-40F	JA2208EXP	191-21-208	SR2PB2-208R3XP
2-11/16	Clearance Seal	Fixed	P2B211C	P2B52-211L	070330	SYR21116H18	USRB5000-211	QAPL15A-211ST	KPB-21116LT	XS2P415-43L	NONE	192-21-211L	SR2PB2-211SLNE
2-11/16	Clearance Seal	Expansion	P2B211CE	P2B52-211LE	070353	SYR2111618	USRB5000E-211	QAPL15A-211SET	NONE	XS2P415-43FL	NONE	191-21-211L	SR2PB2-211SLXP
2-11/16	Triple Lip Seal	Fixed	P2B211T	P2B52-211R	070284	SYR21116H	USRB5000-211C	QAPL15A-211SM	KPB-21116DN	XS2P415-43	JA2211	192-21-211	SR2PB2-211R3NE
2-11/16	Triple Lip Seal	Expansion	P2B211TE	P2B52-211RE	070307	SYR21116	USRB5000E-211C	QAPL15A-211SEM	NONE	XS2P415-43F	JA2211EXP	191-21-211	SR2PB2-211R3XP
2-15/16	Clearance Seal	Fixed	P2B215C	P2B52-215L	070331	SYR21516H18	USRB5000-215	QAPL15A-215ST	NONE	XS2P415-47L	NONE	192-21-215L	SR2PB2-215SLNE
2-15/16	Clearance Seal	Expansion	P2B215CE	P2B52-215LE	070354	SYR2151618	USRB5000E-215	QAPL15A-215SET	NONE	XS2P415-47FL	NONE	191-21-215L	SR2PB2-215SLXP
2-15/16	Triple Lip Seal	Fixed	P2B215T	P2B52-215R	070285	SYR21516H	USRB5000-215C	QAPL15A-215SM	NONE	XS2P415-47	JA2215	192-21-215	SR2PB2-215R3NE
2-15/16	Triple Lip Seal	Expansion	P2B215TE	P2B52-215RE	070308	SYR21516	USRB5000E-215C	QAPL15A-215SEM	NONE	XS2P415-47F	JA2215EXP	191-21-215	SR2PB2-215R3XP
3-7/16	Clearance Seal	Fixed	P2B307C	P2B52-307L	070334	SYR3716H18	USRB5000-307	QAPL18A-307ST	NONE	XS2P418-55L	NONE	192-21-307L	SR2PB2-307SLNE
3-7/16	Clearance Seal	Expansion	P2B307CE	P2B52-307LE	070357	SYR371618	USRB5000E-307	QAPL18A-307SET	NONE	XS2P418-55FL	NONE	191-21-307L	SR2PB2-307SLXP
3-7/16	Triple Lip Seal	Fixed	P2B307T	P2B52-307R	070288	SYR3716H	USRB5000-307C	QAPL18A-307SM	NONE	XS2P418-55	JA2307	192-21-307	SR2PB2-307R3NE
3-7/16	Triple Lip Seal	Expansion	P2B307TE	P2B52-307RE	070311	SYR3716	USRB5000E-307C	QAPL18A-307SEM	NONE	XS2P418-55F	JA2307EXP	191-21-307	SR2PB2-307R3XP
3-1/2	Clearance Seal	Fixed	P2B308C	NONE	NONE	SYR312H18	USRB5000-308	QAPL18A-308ST	NONE	XS2P418-56L	NONE	192-21-308L	SR2PB2-308SLNE
3-1/2	Clearance Seal	Expansion	P2B308CE	NONE	NONE	SYR31218	USRB5000E-308	QAPL18A-308SET	NONE	XS2P418-56FL	NONE	191-21-308L	SR2PB2-308SLXP
3-1/2	Triple Lip Seal	Fixed	P2B308T	NONE	NONE	SYR312H	USRB5000-308C	QAPL18A-308SM	NONE	XS2P418-56	JA2308	192-21-308	SR2PB2-308R3NE
3-1/2	Triple Lip Seal	Expansion	P2B308TE	NONE	NONE	SYR312	USRB5000E-308C	QAPL18A-308SEM	NONE	XS2P418-56F	JA2308EXP	191-21-308	SR2PB2-308R3XP
3-15/16	Clearance Seal	Fixed	P2B315C	P2B52-315L	070336	NONE	NONE	QAPL20A-315ST	NONE	XS2P420-63L	NONE	NONE	SR2PB2-315SLNE
3-15/16	Clearance Seal	Expansion	P2B315CE	P2B52-315LE	070359	NONE	NONE	QAPL20A-315SET	NONE	XS2P420-63FL	NONE	NONE	SR2PB2-315SLXP
3-15/16	Triple Lip Seal	Fixed	P2B315T	P2B52-315R	070290	NONE	NONE	QAPL20A-315SM	NONE	XS2P420-63	NONE	NONE	SR2PB2-315R3NE
3-15/16	Triple Lip Seal	Expansion	P2B315TE	P2B52-315RE	070313	NONE	NONE	QAPL20A-315SEM	NONE	XS2P420-63F	NONE	NONE	SR2PB2-315R3XP

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.



PT Select Housing — 4-Bolt Pillow Block

PT Select

Proven Bearing Quality

Designed with specialized geometry that provides low operating temperatures and reduced vibration, along with premium ingress protection and high speed sealing options. Every PT Select bearing is spin tested under load prior to shipment, and is backed by a two-year warranty*.

Total Cost of Ownership

PT Select is a cost effective, high quality off-the-shelf bearing designed around the characteristics that customers value most.

Valuable Expertise

Rexnord® has been designing and manufacturing high quality products for more than 125 years and is committed to innovating solutions that meet the needs of the customers and industries it serves, now and in the future.

Bore Size	Seal Type	Fixed/ Expansion	PT Select Part Number	Dodge** S2000	Dodge Catalog #	SKF**	Sealmaster	Timken-QM**	Hub City**	FYH**	Jones	Moline**	PTI**
1-15/16	Clearance Seal	Fixed	P4B115C	P4BS2-115L	070397	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
1-15/16	Clearance Seal	Expansion	P4B115CE	P4BS2-115LE	070415	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
1-15/16	Triple Lip Seal	Fixed	P4B115T	P4BS2-115R	070361	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
1-15/16	Triple Lip Seal	Expansion	P4B115TE	P4BS2-115RE	070379	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
2-3/16	Clearance Seal	Fixed	P4B203C	P4BS2-203L	070399	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
2-3/16	Clearance Seal	Expansion	P4B203CE	P4BS2-203LE	070417	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
2-3/16	Triple Lip Seal	Fixed	P4B203T	P4BS2-203R	070363	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
2-3/16	Triple Lip Seal	Expansion	P4B203TE	P4BS2-203RE	070381	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
2-7/16	Clearance Seal	Fixed	P4B207C	P4BS2-207L	070401	NONE	USRBF5000-207	QAPF13A-207ST	NONE	XS4P413-39L	NONE	192-41-207L	NONE
2-7/16	Clearance Seal	Expansion	P4B207CE	P4BS2-207LE	070419	NONE	USRBF5000E-207	QAPF13A-207SET	NONE	XS4P413-39FL	NONE	191-41-207L	NONE
2-7/16	Triple Lip Seal	Fixed	P4B207T	P4BS2-207R	070365	NONE	USRBF5000-207C	QAPF13A-207SM	NONE	XS4P413-39	NONE	192-41-207	NONE
2-7/16	Triple Lip Seal	Expansion	P4B207TE	P4BS2-207RE	070383	NONE	USRBF5000E-207C	QAPF13A-207SEM	NONE	XS4P413-39F	NONE	191-41-207	NONE
2-1/2	Clearance Seal	Fixed	P4B208C	NONE	NONE	NONE	USRBF5000-208	QAPF13A-208ST	NONE	XS4P413-40L	NONE	192-41-208L	NONE
2-1/2	Clearance Seal	Expansion	P4B208CE	NONE	NONE	NONE	USRBF5000E-208	QAPF13A-208SET	NONE	XS4P413-40FL	NONE	191-41-208L	NONE
2-1/2	Triple Lip Seal	Fixed	P4B208T	NONE	NONE	NONE	USRBF5000-208C	QAPF13A-208SM	NONE	XS4P413-40	NONE	192-41-208	NONE
2-1/2	Triple Lip Seal	Expansion	P4B208TE	NONE	NONE	NONE	USRBF5000E-208C	QAPF13A-208SEM	NONE	XS4P413-40F	NONE	191-41-208	NONE
2-11/16	Clearance Seal	Fixed	P4B211C	P4BS2-211L	070403	NONE	USRBF5000-211	QAPF15A-211ST	NONE	XS4P415-43L	NONE	192-41-211L	SR2PB4-211SLNE
2-11/16	Clearance Seal	Expansion	P4B211CE	P4BS2-211LE	070421	NONE	USRBF5000E-211	QAPF15A-211SET	NONE	XS4P415-43FL	NONE	191-41-211L	SR2PB4-211SLXP
2-11/16	Triple Lip Seal	Fixed	P4B211T	P4BS2-211R	070367	NONE	USRBF5000-211C	QAPF15A-211SM	NONE	XS4P415-43	NONE	192-41-211	SR2PB4-211R3NE
2-11/16	Triple Lip Seal	Expansion	P4B211TE	P4BS2-211RE	070385	NONE	USRBF5000E-211C	QAPF15A-211SEM	NONE	XS4P415-43F	NONE	191-41-211	SR2PB4-211R3XP
2-15/16	Clearance Seal	Fixed	P4B215C	P4BS2-215L	070404	NONE	USRBF5000-215	QAPF15A-215ST	NONE	XS4P415-47L	NONE	192-41-215L	SR2PB4-215SLNE
2-15/16	Clearance Seal	Expansion	P4B215CE	P4BS2-215LE	070422	NONE	USRBF5000E-215	QAPF15A-215SET	NONE	XS4P415-47FL	NONE	191-41-215L	SR2PB4-215SLXP
2-15/16	Triple Lip Seal	Fixed	P4B215T	P4BS2-215R	070368	NONE	USRBF5000-215C	QAPF15A-215SM	NONE	XS4P415-47	NONE	192-41-215	SR2PB4-215R3NE
2-15/16	Triple Lip Seal	Expansion	P4B215TE	P4BS2-215RE	070386	NONE	USRBF5000E-215C	QAPF15A-215SEM	NONE	XS4P415-47F	NONE	191-41-215	SR2PB4-215R3XP
3-7/16	Clearance Seal	Fixed	P4B307C	P4BS2-307L	070407	NONE	USRBF5000-307	QAPF18A-307ST	NONE	XS4P418-55L	NONE	192-41-307L	SR2PB4-307SLNE
3-7/16	Clearance Seal	Expansion	P4B307CE	P4BS2-307LE	070425	NONE	USRBF5000E-307	QAPF18A-307SET	NONE	XS4P418-55FL	NONE	191-41-307L	SR2PB4-307SLXP
3-7/16	Triple Lip Seal	Fixed	P4B307T	P4BS2-307R	070371	NONE	USRBF5000-307C	QAPF18A-307SM	NONE	XS4P418-55	NONE	192-41-307	SR2PB4-307R3NE
3-7/16	Triple Lip Seal	Expansion	P4B307TE	P4BS2-307RE	070389	NONE	USRBF5000E-307C	QAPF18A-307SEM	NONE	XS4P418-55F	NONE	191-41-307	SR2PB4-307R3XP
3-1/2	Clearance Seal	Fixed	P4B308C	NONE	NONE	NONE	USRBF5000-308	QAPF18A-308ST	NONE	XS4P418-56L	NONE	192-41-308L	SR2PB4-308SLNE
3-1/2	Clearance Seal	Expansion	P4B308CE	NONE	NONE	NONE	USRBF5000E-308	QAPF18A-308SET	NONE	XS4P418-56FL	NONE	191-41-308L	SR2PB4-308SLXP
3-1/2	Triple Lip Seal	Fixed	P4B308T	NONE	NONE	NONE	USRBF5000-308C	QAPF18A-308SM	NONE	XS4P418-56	NONE	192-41-308	SR2PB4-308R3NE
3-1/2	Triple Lip Seal	Expansion	P4B308TE	NONE	NONE	NONE	USRBF5000E-308C	QAPF18A-308SEM	NONE	XS4P418-56F	NONE	191-41-308	SR2PB4-308R3XP
3-15/16	Clearance Seal	Fixed	P4B315C	P4BS2-315L	070409	NONE	USRBF5000-315	QAPF20A-315ST	NONE	XS4P420-63L	NONE	192-41-315L	SR2PB4-315SLNE
3-15/16	Clearance Seal	Expansion	P4B315CE	P4BS2-315LE	070427	NONE	USRBF5000E-315	QAPF20A-315SET	NONE	XS4P420-63FL	NONE	191-41-315L	SR2PB4-315SLXP
3-15/16	Triple Lip Seal	Fixed	P4B315T	P4BS2-315R	070373	NONE	USRBF5000-315C	QAPF20A-315SM	NONE	XS4P420-63	NONE	192-41-315	SR2PB4-315R3NE
3-15/16	Triple Lip Seal	Expansion	P4B315TE	P4BS2-315RE	070391	NONE	USRBF5000E-315C	QAPF20A-315SEM	NONE	XS4P420-63F	NONE	191-41-315	SR2PB4-315R3XP
4-7/16	Clearance Seal	Fixed	P4B407C	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Clearance Seal	Expansion	P4B407CE	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Triple Lip Seal	Fixed	P4B407T	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE
4-7/16	Triple Lip Seal	Expansion	P4B407TE	NONE	NONE	NONE	NONE	NONE	NONE	#N/A	NONE	NONE	NONE

* Two-year warranty requires registration of the bearing at Rexnord.com

** This trademark or trade name is owned or controlled by a third party and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

SKF®* — PT Select Interchange Guide

SKF	PT Select
FYE11116	EFB111TE
FYE1111618	EFB111CE
FYE11116H	EFB111T
FYE11116H18	EFB111C
FYE11516	EFB115TE
FYE1151618	EFB115CE
FYE11516H	EFB115T
FYE11516H18	EFB115C
FYE1716	EFB107TE
FYE171618	EFB107CE
FYE1716H	EFB107T
FYE1716H18	EFB107C
FYE21116	EFB211TE
FYE2111618	EFB211CE
FYE21116H	EFB211T
FYE21116H18	EFB211C
FYE212	EFB208TE
FYE21218	EFB208CE
FYE212H	EFB208T
FYE212H18	EFB208C
FYE21516	EFB215TE
FYE2151618	EFB215CE
FYE21516H	EFB215T
FYE21516H18	EFB215C
FYE2316	EFB203TE
FYE231618	EFB203CE
FYE2316H	EFB203T
FYE2316H18	EFB203C
FYE2716	EFB207TE
FYE271618	EFB207CE
FYE2716H	EFB207T
FYE2716H18	EFB207C
FYE312	EFB308TE
FYE31218	EFB308CE
FYE312H	EFB308T
FYE312H18	EFB308C
FYE31516	EFB315TE
FYE3151618	EFB315CE
FYE31516H	EFB315T
FYE31516H18	EFB315C
FYE3716	EFB307TE
FYE371618	EFB307CE
FYE3716H	EFB307T
FYE3716H18	EFB307C
FYR11116	FB111TE
FYR1111618	FB111CE
FYR11116H	FB111T
FYR11116H18	FB111C
FYR11516	FB115TE
FYR1151618	FB115CE
FYR11516H	FB115T
FYR11516H18	FB115C
FYR1716	FB107TE
FYR171618	FB107CE
FYR1716H	FB107T
FYR1716H18	FB107C
FYR21116	FB211TE
FYR2111618	FB211CE
FYR21116H	FB211T
FYR21116H18	FB211C
FYR212	FB208TE
FYR21218	FB208CE
FYR212H	FB208T

SKF	PT Select
FYR212H18	FB208C
FYR21516	FB215TE
FYR2151618	FB215CE
FYR21516H	FB215T
FYR21516H18	FB215C
FYR2316	FB203TE
FYR231618	FB203CE
FYR2316H	FB203T
FYR2316H18	FB203C
FYR2716	FB207TE
FYR271618	FB207CE
FYR2716H	FB207T
FYR2716H18	FB207C
FYR312	FB308TE
FYR31218	FB308CE
FYR312H	FB308T
FYR312H18	FB308C
FYR315	FB315TE
FYR31518	FB315CE
FYR315H	FB315T
FYR315H18	FB315C
FYR3716	FB307TE
FYR371618	FB307CE
FYR3716H	FB307T
FYR3716H18	FB307C
FYRP11116	FC111TE
FYRP1111618	FC111CE
FYRP11116H	FC111T
FYRP11116H18	FC111C
FYRP11516	FC115TE
FYRP1151618	FC115CE
FYRP11516H	FC115T
FYRP11516H18	FC115C
FYRP1716	FC107TE
FYRP171618	FC107CE
FYRP1716H	FC107T
FYRP1716H18	FC107C
FYRP21116	FC211TE
FYRP2111618	FC211CE
FYRP21116H	FC211T
FYRP21116H18	FC211C
FYRP212	FC208TE
FYRP21218	FC208CE
FYRP212H	FC208T
FYRP212H18	FC208C
FYRP21516	FC215TE
FYRP2151618	FC215CE
FYRP21516H	FC215T
FYRP21516H18	FC215C
FYRP2316	FC203TE
FYRP231618	FC203CE
FYRP2316H	FC203T
FYRP2316H18	FC203C
FYRP2716	FC207TE
FYRP271618	FC207CE
FYRP2716H	FC207T
FYRP2716H18	FC207C
FYRP312	FC308TE
FYRP31218	FC308CE
FYRP312H	FC308T
FYRP312H18	FC308C
FYRP315	FC315TE
FYRP31518	FC315CE

SKF	PT Select
FYRP315H	FC315T
FYRP315H18	FC315C
FYRP3716	FC307TE
FYRP371618	FC307CE
FYRP3716H	FC307T
FYRP3716H18	FC307C
SYE11116	EP2B111TE
SYE1111618	EP2B111CE
SYE11116H	EP2B111T
SYE11116H18	EP2B111C
SYE11516	EP2B115TE
SYE1151618	EP2B115CE
SYE11516H	EP2B115T
SYE11516H18	EP2B115C
SYE1716	EP2B107TE
SYE171618	EP2B107CE
SYE1716H	EP2B107T
SYE1716H18	EP2B107C
SYE21116	EP2B211TE
SYE2111618	EP2B211CE
SYE21116H	EP2B211T
SYE21116H18	EP2B211C
SYE212	EP2B208TE
SYE21218	EP2B208CE
SYE212H	EP2B208T
SYE212H18	EP2B208C
SYE21516	EP2B215TE
SYE2151618	EP2B215CE
SYE21516H	EP2B215T
SYE21516H18	EP2B215C
SYE2316	EP2B203TE
SYE231618	EP2B203CE
SYE2316H	EP2B203T
SYE2316H18	EP2B203C
SYE2716	EP2B207TE
SYE271618	EP2B207CE
SYE2716H	EP2B207T
SYE2716H18	EP2B207C
SYE3716	EP2B307TE
SYE371618	EP2B307CE
SYE3716H	EP2B307T
SYE3716H18	EP2B307C
SYR11116	P2B111TE
SYR1111618	P2B111CE
SYR11116H	P2B111T
SYR11116H18	P2B111C
SYR11516	P2B115TE
SYR1151618	P2B115CE
SYR11516H	P2B115T
SYR11516H18	P2B115C
SYR1716	P2B107TE
SYR171618	P2B107CE
SYR1716H	P2B107T
SYR1716H18	P2B107C
SYR21116	P2B211TE
SYR2111618	P2B211CE
SYR21116H	P2B211T
SYR21116H18	P2B211C
SYR212	P2B208TE
SYR21218	P2B208CE
SYR212H	P2B208T
SYR212H18	P2B208C
SYR21516	P2B215TE

SKF	PT Select
SYR2151618	P2B215CE
SYR21516H	P2B215T
SYR21516H18	P2B215C
SYR2316	P2B203TE
SYR231618	P2B203CE
SYR2316H	P2B203T
SYR2316H18	P2B203C
SYR2716	P2B207TE
SYR271618	P2B207CE
SYR2716H	P2B207T
SYR2716H18	P2B207C
SYR312	P2B308TE
SYR31218	P2B308CE
SYR312H	P2B308T
SYR312H18	P2B308C
SYR3716	P2B307TE
SYR371618	P2B307CE
SYR3716H	P2B307T
SYR3716H18	P2B307C

* SKF is believed to be the trademark and/or trade name of Aktiebolaget SKF and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

FYH®* — PT Select Interchange Guide

FYH	PT Select
XS2P408-23	P2B107T
XS2P408-23F	P2B107TE
XS2P408-23FL	P2B107CE
XS2P408-23L	P2B107C
XS2P409-27	P2B111T
XS2P409-27F	P2B111TE
XS2P409-27FL	P2B111CE
XS2P409-27L	P2B111C
XS2P410-31	P2B115T
XS2P410-31F	P2B115TE
XS2P410-31FL	P2B115CE
XS2P410-31L	P2B115C
XS2P411-35	P2B203T
XS2P411-35F	P2B203TE
XS2P411-35FL	P2B203CE
XS2P411-35L	P2B203C
XS2P413-39	P2B207T
XS2P413-39F	P2B207TE
XS2P413-39FL	P2B207CE
XS2P413-39L	P2B207C
XS2P413-40	P2B208T
XS2P413-40F	P2B208TE
XS2P413-40FL	P2B208CE
XS2P413-40L	P2B208C
XS2P415-43	P2B211T
XS2P415-43F	P2B211TE
XS2P415-43FL	P2B211CE
XS2P415-43L	P2B211C
XS2P415-47	P2B215T
XS2P415-47F	P2B215TE
XS2P415-47FL	P2B215CE
XS2P415-47L	P2B215C
XS2P418-55	P2B307T
XS2P418-55F	P2B307TE
XS2P418-55FL	P2B307CE
XS2P418-55L	P2B307C
XS2P418-56	P2B308T
XS2P418-56F	P2B308TE
XS2P418-56FL	P2B308CE
XS2P418-56L	P2B308C
XS2P420-63	P2B315T
XS2P420-63F	P2B315TE
XS2P420-63FL	P2B315CE
XS2P420-63L	P2B315C
XS4F408-23	FB107T
XS4F408-23F	FB107TE
XS4F408-23FL	FB107CE
XS4F408-23L	FB107C
XS4F409-27	FB111T
XS4F409-27F	FB111TE
XS4F409-27FL	FB111CE
XS4F409-27L	FB111C
XS4F410-31	FB115T
XS4F410-31F	FB115TE
XS4F410-31FL	FB115CE
XS4F410-31L	FB115C
XS4F411-35	FB203T
XS4F411-35F	FB203TE
XS4F411-35FL	FB203CE
XS4F411-35L	FB203C
XS4F413-39	FB207T
XS4F413-39F	FB207TE
XS4F413-39FL	FB207CE
XS4F413-39L	FB207C

FYH	PT Select
XS4F413-39L	FB207C
XS4F413-40	FB208T
XS4F413-40F	FB208TE
XS4F413-40FL	FB208CE
XS4F413-40L	FB208C
XS4F415-43	FB211T
XS4F415-43F	FB211TE
XS4F415-43FL	FB211CE
XS4F415-43L	FB211C
XS4F415-47	FB215T
XS4F415-47F	FB215TE
XS4F415-47FL	FB215CE
XS4F415-47L	FB215C
XS4F418-55	FB307T
XS4F418-55F	FB307TE
XS4F418-55FL	FB307CE
XS4F418-55L	FB307C
XS4F418-56	FB308T
XS4F418-56F	FB308TE
XS4F418-56FL	FB308CE
XS4F418-56L	FB308C
XS4F420-63	FB315T
XS4F420-63F	FB315TE
XS4F420-63FL	FB315CE
XS4F420-63L	FB315C
XS4FC408-23	FC107T
XS4FC408-23F	FC107TE
XS4FC408-23FL	FC107CE
XS4FC408-23L	FC107C
XS4FC409-27	FC111T
XS4FC409-27F	FC111TE
XS4FC409-27FL	FC111CE
XS4FC409-27L	FC111C
XS4FC410-31	FC115T
XS4FC410-31F	FC115TE
XS4FC410-31FL	FC115CE
XS4FC410-31L	FC115C
XS4FC411-35	FC203T
XS4FC411-35F	FC203TE
XS4FC411-35FL	FC203CE
XS4FC411-35L	FC203C
XS4FC413-39	FC207T
XS4FC413-39F	FC207TE
XS4FC413-39FL	FC207CE
XS4FC413-39L	FC207C
XS4FC413-40	FC208T
XS4FC413-40F	FC208TE
XS4FC413-40FL	FC208CE
XS4FC413-40L	FC208C
XS4FC415-43	FC211T
XS4FC415-43F	FC211TE
XS4FC415-43FL	FC211CE
XS4FC415-43L	FC211C
XS4FC415-47	FC215T
XS4FC415-47F	FC215TE
XS4FC415-47FL	FC215CE
XS4FC415-47L	FC215C
XS4FC418-55	FC307T
XS4FC418-55F	FC307TE
XS4FC418-55FL	FC307CE
XS4FC418-55L	FC307C
XS4FC418-56	FC308T
XS4FC418-56F	FC308TE
XS4FC418-56FL	FC308CE
XS4FC418-56L	FC308C

FYH	PT Select
XS4FC418-56FL	FC308CE
XS4FC418-56L	FC308C
XS4FC420-63	FC315T
XS4FC420-63F	FC315TE
XS4FC420-63FL	FC315CE
XS4FC420-63L	FC315C
XS4P413-39	P4B207T
XS4P413-39F	P4B207TE
XS4P413-39FL	P4B207CE
XS4P413-39L	P4B207C
XS4P413-40	P4B208T
XS4P413-40F	P4B208TE
XS4P413-40FL	P4B208CE
XS4P413-40L	P4B208C
XS4P415-43	P4B211T
XS4P415-43F	P4B211TE
XS4P415-43FL	P4B211CE
XS4P415-43L	P4B211C
XS4P415-47	P4B215T
XS4P415-47F	P4B215TE
XS4P415-47FL	P4B215CE
XS4P415-47L	P4B215C
XS4P418-55	P4B307T
XS4P418-55F	P4B307TE
XS4P418-55FL	P4B307CE
XS4P418-55L	P4B307C
XS4P418-56	P4B308T
XS4P418-56F	P4B308TE
XS4P418-56FL	P4B308CE
XS4P418-56L	P4B308C
XS4P420-63	P4B315T
XS4P420-63F	P4B315TE
XS4P420-63FL	P4B315CE
XS4P420-63L	P4B315C
XSE2P408-23	EP2B107T
XSE2P408-23F	EP2B107TE
XSE2P408-23FL	EP2B107CE
XSE2P408-23L	EP2B107C
XSE2P409-27	EP2B111T
XSE2P409-27F	EP2B111TE
XSE2P409-27FL	EP2B111CE
XSE2P409-27L	EP2B111C
XSE2P410-31	EP2B115T
XSE2P410-31F	EP2B115TE
XSE2P410-31FL	EP2B115CE
XSE2P410-31L	EP2B115C
XSE2P411-35	EP2B203T
XSE2P411-35F	EP2B203TE
XSE2P411-35FL	EP2B203CE
XSE2P411-35L	EP2B203C
XSE2P413-39	EP2B207T
XSE2P413-39F	EP2B207TE
XSE2P413-39FL	EP2B207CE
XSE2P413-39L	EP2B207C
XSE2P413-40	EP2B208T
XSE2P413-40F	EP2B208TE
XSE2P413-40FL	EP2B208CE
XSE2P413-40L	EP2B208C
XSE2P415-43	EP2B211T
XSE2P415-43F	EP2B211TE
XSE2P415-43FL	EP2B211CE
XSE2P415-43L	EP2B211C
XSE2P415-47	EP2B215T

FYH	PT Select
XSE2P415-47F	EP2B215TE
XSE2P415-47FL	EP2B215CE
XSE2P415-47L	EP2B215C
XSE2P418-55	EP2B307T
XSE2P418-55F	EP2B307TE
XSE2P418-55FL	EP2B307CE
XSE2P418-55L	EP2B307C
XSE2P418-56	EP2B308T
XSE2P418-56F	EP2B308TE
XSE2P418-56FL	EP2B308CE
XSE2P418-56L	EP2B308C
XSE4F408-23	EFB107T
XSE4F408-23F	EFB107TE
XSE4F408-23FL	EFB107CE
XSE4F408-23L	EFB107C
XSE4F409-27	EFB111T
XSE4F409-27F	EFB111TE
XSE4F409-27FL	EFB111CE
XSE4F409-27L	EFB111C
XSE4F410-31	EFB115T
XSE4F410-31F	EFB115TE
XSE4F410-31FL	EFB115CE
XSE4F410-31L	EFB115C
XSE4F411-35	EFB203T
XSE4F411-35F	EFB203TE
XSE4F411-35FL	EFB203CE
XSE4F411-35L	EFB203C
XSE4F413-39	EFB207T
XSE4F413-39F	EFB207TE
XSE4F413-39FL	EFB207CE
XSE4F413-39L	EFB207C
XSE4F413-40	EFB208T
XSE4F413-40F	EFB208TE
XSE4F413-40FL	EFB208CE
XSE4F413-40L	EFB208C
XSE4F415-43	EFB211T
XSE4F415-43F	EFB211TE
XSE4F415-43FL	EFB211CE
XSE4F415-43L	EFB211C
XSE4F415-47	EFB215T
XSE4F415-47F	EFB215TE
XSE4F415-47FL	EFB215CE
XSE4F415-47L	EFB215C
XSE4F418-55	EFB307T
XSE4F418-55F	EFB307TE
XSE4F418-55FL	EFB307CE
XSE4F418-55L	EFB307C
XSE4F418-56	EFB308T
XSE4F418-56F	EFB308TE
XSE4F418-56FL	EFB308CE
XSE4F418-56L	EFB308C
XSE4F420-63	EFB315T
XSE4F420-63F	EFB315TE
XSE4F420-63FL	EFB315CE
XSE4F420-63L	EFB315C

Hub City®* — PT Select Interchange Guide

Hub City	PT Select
KFB-11116DN	FB111T
KFB-11116LT	FB111C
KFB-11116TN	FB111T
KFB-11516DN	FB115T
KFB-11516LT	FB115C
KFB-11516TN	FB115T
KFB-1716DN	FB107T
KFB-1716LT	FB107C
KFB-1716TN	FB107T
KFB-21116DN	FB211T
KFB-21116LT	FB211C
KFB-21116TN	FB211T
KFB-212DN	FB208T
KFB-212LT	FB208C
KFB-212TN	FB208T
KFB-21516DN	FB215T
KFB-21516LT	FB215C
KFB-21516TN	FB215T
KFB-2316DN	FB203T
KFB-2316LT	FB203C
KFB-2316TN	FB203T
KFB-2716DN	FB207T
KFB-2716LT	FB207C
KFB-2716TN	FB207T
KFB-312DN	FB308T
KFB-312LT	FB308C
KFB-312TN	FB308T
KFB-31516DN	FB315T
KFB-31516LT	FB315C
KFB-31516TN	FB315T
KFB-3716DN	FB307T
KFB-3716LT	FB307C
KFB-3716TN	FB307T
KFB-4DN	FB22464E
KFB-4LT	FB22464H
KFB-4TN	FB22464E
KFBE-11116DN	EFB111T
KFBE-11116LT	EFB111C
KFBE-11116TN	EFB111T
KFBE-11516DN	EFB115T
KFBE-11516LT	EFB115C
KFBE-11516TN	EFB115T
KFBE-1716DN	EFB107T
KFBE-1716LT	EFB107C
KFBE-1716TN	EFB107T
KFBE-21116DN	EFB211T
KFBE-21116LT	EFB211C
KFBE-21116TN	EFB211T
KFBE-212DN	EFB208T
KFBE-212LT	EFB208C
KFBE-212TN	EFB208T
KFBE-21516DN	EFB215T
KFBE-21516LT	EFB215C
KFBE-21516TN	EFB215T
KFBE-2316DN	EFB203T
KFBE-2316LT	EFB203C
KFBE-2316TN	EFB203T
KFBE-2716DN	EFB207T
KFBE-2716LT	EFB207C
KFBE-2716TN	EFB207T
KFBE-312DN	EFB308T
KFBE-312LT	EFB308C
KFBE-312TN	EFB308T

Hub City	PT Select
KFBE-31516DN	EFB315T
KFBE-31516LT	EFB315C
KFBE-31516TN	EFB315T
KFBE-3716DN	EFB307T
KFBE-3716LT	EFB307C
KFBE-3716TN	EFB307T
KPB-11116DN	P2B111T
KPB-11116LT	P2B111C
KPB-11116TN	P2B111T
KPB-11516DN	P2B115T
KPB-11516LT	P2B115C
KPB-11516TN	P2B115T
KPB-1716DN	P2B107T
KPB-1716LT	P2B107C
KPB-1716TN	P2B107T
KPB-21116DN	P2B211T
KPB-21116LT	P2B211C
KPB-21116TN	P2B211T
KPB-212DN	P2B208T
KPB-212LT	P2B208C
KPB-212TN	P2B208T
KPB-2316DN	P2B203T
KPB-2316LT	P2B203C
KPB-2316TN	P2B203T
KPB-2716DN	P2B207T
KPB-2716LT	P2B207C
KPB-2716TN	P2B207T
KPBE-11116DN	EP2B111T
KPBE-11116LT	EP2B111C
KPBE-11116TN	EP2B111T
KPBE-11516DN	EP2B115T
KPBE-11516LT	EP2B115C
KPBE-11516TN	EP2B115T
KPBE-1716DN	EP2B107T
KPBE-1716LT	EP2B107C
KPBE-1716TN	EP2B107T
KPBE-21116DN	EP2B211T
KPBE-21116LT	EP2B211C
KPBE-21116TN	EP2B211T
KPBE-212DN	EP2B208T
KPBE-212LT	EP2B208C
KPBE-212TN	EP2B208T
KPBE-2316DN	EP2B203T
KPBE-2316LT	EP2B203C
KPBE-2316TN	EP2B203T
KPBE-2716DN	EP2B207T
KPBE-2716LT	EP2B207C
KPBE-2716TN	EP2B207T

* Hub City is believed to be the trademark and/or trade name of Hub City, Inc. and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

Jones — PT Select Interchange Guide

Jones	PT Select
JA2107	P2B107T
JA2107EXP	P2B107TE
JA2111	P2B111T
JA2111EXP	P2B111TE
JA2115	P2B115T
JA2115EXP	P2B115TE
JA2203	P2B203T
JA2203EXP	P2B203TE
JA2207	P2B207T
JA2207EXP	P2B207TE
JA2208	P2B208T
JA2208EXP	P2B208TE
JA2211	P2B211T
JA2211EXP	P2B211TE
JA2215	P2B215T
JA2215EXP	P2B215TE
JA2307	P2B307T
JA2307EXP	P2B307TE
JA2308	P2B308T
JA2308EXP	P2B308TE
JE2107	EP2B107T
JE2107EXP	EP2B107TE
JE2111	EP2B111T
JE2111EXP	EP2B111TE
JE2115	EP2B115T
JE2115EXP	EP2B115TE
JE2203	EP2B203T
JE2203EXP	EP2B203TE
JE2207	EP2B207T
JE2207EXP	EP2B207TE
JE2208	EP2B208T
JE2208EXP	EP2B208TE
JE2211	EP2B211T
JE2211EXP	EP2B211TE
JE2215	EP2B215T
JE2215EXP	EP2B215TE
JE2307	EP2B307T
JE2307EXP	EP2B307TE
JE2308	EP2B308T
JE2308EXP	EP2B308TE
JYR2111	FB111T
JYR2111EXP	FB111TE
JYR2115	FB115T
JYR2115EXP	FB115TE
JYR2203	FB203T
JYR2203EXP	FB203TE
JYR2207	FB207T
JYR2207EXP	FB207TE
JYR2208	FB208T
JYR2208EXP	FB208TE
JYR2211	FB211T
JYR2211EXP	FB211TE
JYR2215	FB215T
JYR2215EXP	FB215TE
JYR2307	FB307T
JYR2307EXP	FB307TE
JYR2307S	FB307T
JYR2307SEXP	FB307TE
JYR2308	FB308T
JYR2308EXP	FB308TE
JYR2308S	FB308T
JYR2308SEXP	FB308TE

Jones	PT Select
JYR2315	FB315T
JYR2315EXP	FB315TE
JYR2315S	FB315T
JYR2315SEXP	FB315TE
JYRP2107	FC107T
JYRP2107EXP	FC107TE
JYRP2111	FC111T
JYRP2111EXP	FC111TE
JYRP2115	FC115T
JYRP2115EXP	FC115TE
JYRP2203	FC203T
JYRP2203EXP	FC203TE
JYRP2207	FC207T
JYRP2207EXP	FC207TE
JYRP2208	FC208T
JYRP2208EXP	FC208TE
JYRP2211	FC211T
JYRP2211EXP	FC211TE
JYRP2215	FC215T
JYRP2215EXP	FC215TE
JYRP2307	FC307T
JYRP2307EXP	FC307TE
JYRP2308	FC308T
JYRP2308EXP	FC308TE
JYRP2315	FC315T
JYRP2315EXP	FC315TE

Moline®* — PT Select Interchange Guide

Moline	PT Select	Moline	PT Select	Moline	PT Select	Moline	PT Select	Moline	PT Select	Moline	PT Select
191-11-107	FB107TE	191-31-115L	FC115CE	192-11-307G	FB307T	192-41-207	P4B207T	291-21-208L	EP2B208CE	292-11-308G	EFB308T
191-11-107G	FB107TE	191-31-203	FC203TE	192-11-307L	FB307C	192-41-207G	P4B207T	291-21-211	EP2B211TE	292-11-308L	EFB308C
191-11-107L	FB107CE	191-31-203G	FC203TE	192-11-308	FB308T	192-41-207L	P4B207C	291-21-211G	EP2B211TE	292-11-315	EFB315T
191-11-111	FB111TE	191-31-203L	FC203CE	192-11-308G	FB308T	192-41-208	P4B208T	291-21-211L	EP2B211CE	292-11-315G	EFB315T
191-11-111G	FB111TE	191-31-207	FC207TE	192-11-308L	FB308C	192-41-208G	P4B208T	291-21-215	EP2B215TE	292-11-315L	EFB315C
191-11-111L	FB111CE	191-31-207G	FC207TE	192-11-315	FB315T	192-41-208L	P4B208C	291-21-215G	EP2B215TE	292-21-107	EP2B107T
191-11-115	FB115TE	191-31-207L	FC207CE	192-11-315G	FB315T	192-41-211	P4B211T	291-21-215L	EP2B215CE	292-21-107G	EP2B107T
191-11-115G	FB115TE	191-31-208	FC208TE	192-11-315L	FB315C	192-41-211G	P4B211T	291-21-307	EP2B307TE	292-21-107L	EP2B107C
191-11-115L	FB115CE	191-31-208G	FC208TE	192-21-107	P2B107T	192-41-211L	P4B211C	291-21-307G	EP2B307TE	292-21-111	EP2B111T
191-11-203	FB203TE	191-31-208L	FC208CE	192-21-107G	P2B107T	192-41-215	P4B215T	291-21-307L	EP2B307CE	292-21-111G	EP2B111T
191-11-203G	FB203TE	191-31-211	FC211TE	192-21-107L	P2B107C	192-41-215G	P4B215T	291-21-308	EP2B308TE	292-21-111L	EP2B111C
191-11-203L	FB203CE	191-31-211G	FC211TE	192-21-111	P2B111T	192-41-215L	P4B215C	291-21-308G	EP2B308TE	292-21-115	EP2B115T
191-11-207	FB207TE	191-31-211L	FC211CE	192-21-111G	P2B111T	192-41-307	P4B307T	291-21-308L	EP2B308CE	292-21-115G	EP2B115T
191-11-207G	FB207TE	191-31-215	FC215TE	192-21-111L	P2B111C	192-41-307G	P4B307T	291-31-111	FC111TE	292-21-115L	EP2B115C
191-11-207L	FB207CE	191-31-215G	FC215TE	192-21-115	P2B115T	192-41-307L	P4B307C	291-31-111G	FC111TE	292-21-203	EP2B203T
191-11-208	FB208TE	191-31-215L	FC215CE	192-21-115G	P2B115T	192-41-308	P4B308T	291-31-111L	FC111CE	292-21-203G	EP2B203T
191-11-208G	FB208TE	191-31-307	FC307TE	192-21-115L	P2B115C	192-41-308G	P4B308T	291-31-115	FC115TE	292-21-203L	EP2B203C
191-11-208L	FB208CE	191-31-307G	FC307TE	192-21-203	P2B203T	192-41-308L	P4B308C	291-31-115G	FC115TE	292-21-207	EP2B207T
191-11-211	FB211TE	191-31-307L	FC307CE	192-21-203G	P2B203T	192-41-315	P4B315T	291-31-115L	FC115CE	292-21-207G	EP2B207T
191-11-211G	FB211TE	191-31-308	FC308TE	192-21-203L	P2B203C	192-41-315G	P4B315T	291-31-203	FC203TE	292-21-207L	EP2B207C
191-11-211L	FB211CE	191-31-308G	FC308TE	192-21-207	P2B207T	192-41-315L	P4B315C	291-31-203G	FC203TE	292-21-208	EP2B208T
191-11-215	FB215TE	191-31-308L	FC308CE	192-21-207G	P2B207T	291-11-107	EFB107TE	291-31-203L	FC203CE	292-21-208G	EP2B208T
191-11-215G	FB215TE	191-31-315	FC315TE	192-21-207L	P2B207C	291-11-107G	EFB107TE	291-31-207	FC207TE	292-21-208L	EP2B208C
191-11-215L	FB215CE	191-31-315G	FC315TE	192-21-208	P2B208T	291-11-107L	EFB107CE	291-31-207G	FC207TE	292-21-211	EP2B211T
191-11-307	FB307TE	191-31-315L	FC315CE	192-21-208G	P2B208T	291-11-111	EFB111TE	291-31-207L	FC207CE	292-21-211G	EP2B211T
191-11-307G	FB307TE	191-41-207	P4B207TE	192-21-208L	P2B208C	291-11-111G	EFB111TE	291-31-208	FC208TE	292-21-211L	EP2B211C
191-11-307L	FB307CE	191-41-207G	P4B207TE	192-21-211	P2B211T	291-11-111L	EFB111CE	291-31-208G	FC208TE	292-21-215	EP2B215T
191-11-308	FB308TE	191-41-207L	P4B207CE	192-21-211G	P2B211T	291-11-115	EFB115TE	291-31-208L	FC208CE	292-21-215G	EP2B215T
191-11-308G	FB308TE	191-41-208	P4B208TE	192-21-211L	P2B211C	291-11-115G	EFB115TE	291-31-211	FC211TE	292-21-215L	EP2B215C
191-11-308L	FB308CE	191-41-208G	P4B208TE	192-21-215	P2B215T	291-11-115L	EFB115CE	291-31-211G	FC211TE	292-21-307	EP2B307T
191-11-315	FB315TE	191-41-208L	P4B208CE	192-21-215G	P2B215T	291-11-203	EFB203TE	291-31-211L	FC211CE	292-21-307G	EP2B307T
191-11-315G	FB315TE	191-41-211	P4B211TE	192-21-215L	P2B215C	291-11-203G	EFB203TE	291-31-215	FC215TE	292-21-307L	EP2B307C
191-11-315L	FB315CE	191-41-211G	P4B211TE	192-21-307	P2B307T	291-11-203L	EFB203CE	291-31-215G	FC215TE	292-21-308	EP2B308T
191-21-107	P2B107TE	191-41-211L	P4B211CE	192-21-307G	P2B307T	291-11-207	EFB207TE	291-31-215L	FC215CE	292-21-308G	EP2B308T
191-21-107G	P2B107TE	191-41-215	P4B215TE	192-21-307L	P2B307C	291-11-207G	EFB207TE	291-31-307	FC307TE	292-21-308L	EP2B308C
191-21-107L	P2B107CE	191-41-215G	P4B215TE	192-21-308	P2B308T	291-11-207L	EFB207CE	291-31-307G	FC307TE	292-31-111	FC111T
191-21-111	P2B111TE	191-41-215L	P4B215CE	192-21-308G	P2B308T	291-11-208	EFB208TE	291-31-307L	FC307CE	292-31-111G	FC111T
191-21-111G	P2B111TE	191-41-307	P4B307TE	192-21-308L	P2B308C	291-11-208G	EFB208TE	291-31-308	FC308TE	292-31-111L	FC111C
191-21-111L	P2B111CE	191-41-307G	P4B307TE	192-31-107	FC107T	291-11-208L	EFB208CE	291-31-308G	FC308TE	292-31-115	FC115T
191-21-115	P2B115TE	191-41-307L	P4B307CE	192-31-107G	FC107T	291-11-211	EFB211TE	291-31-308L	FC308CE	292-31-115G	FC115T
191-21-115G	P2B115TE	191-41-308	P4B308TE	192-31-107L	FC107C	291-11-211G	EFB211TE	291-31-315	FC315TE	292-31-115L	FC115C
191-21-115L	P2B115CE	191-41-308G	P4B308TE	192-31-111	FC111T	291-11-211L	EFB211CE	291-31-315G	FC315TE	292-31-203	FC203T
191-21-203	P2B203TE	191-41-308L	P4B308CE	192-31-111G	FC111T	291-11-215	EFB215TE	291-31-315L	FC315CE	292-31-203G	FC203T
191-21-203G	P2B203TE	191-41-315	P4B315TE	192-31-111L	FC111C	291-11-215G	EFB215TE	292-11-107	EFB107T	292-31-203L	FC203C
191-21-203L	P2B203CE	191-41-315G	P4B315TE	192-31-115	FC115T	291-11-215L	EFB215CE	292-11-107G	EFB107T	292-31-207	FC207T
191-21-207	P2B207TE	191-41-315L	P4B315CE	192-31-115G	FC115T	291-11-307	EFB307TE	292-11-107L	EFB107C	292-31-207G	FC207T
191-21-207G	P2B207TE	192-11-107	FB107T	192-31-115L	FC115C	291-11-307G	EFB307TE	292-11-111	EFB111T	292-31-207L	FC207C
191-21-207L	P2B207CE	192-11-107G	FB107T	192-31-203	FC203T	291-11-307L	EFB307CE	292-11-111G	EFB111T	292-31-208	FC208T
191-21-208	P2B208TE	192-11-107L	FB107C	192-31-203G	FC203T	291-11-308	EFB308TE	292-11-111L	EFB111C	292-31-208G	FC208T
191-21-208G	P2B208TE	192-11-111	FB111T	192-31-203L	FC203C	291-11-308G	EFB308TE	292-11-115	EFB115T	292-31-208L	FC208C
191-21-208L	P2B208CE	192-11-111G	FB111T	192-31-207	FC207T	291-11-308L	EFB308CE	292-11-115G	EFB115T	292-31-211	FC211T
191-21-211	P2B211TE	192-11-111L	FB111C	192-31-207G	FC207T	291-11-315	EFB315TE	292-11-115L	EFB115C	292-31-211G	FC211T
191-21-211G	P2B211TE	192-11-115	FB115T	192-31-207L	FC207C	291-11-315G	EFB315TE	292-11-203	EFB203T	292-31-211L	FC211C
191-21-211L	P2B211CE	192-11-115G	FB115T	192-31-208	FC208T	291-11-315L	EFB315CE	292-11-203G	EFB203T	292-31-215	FC215T
191-21-215	P2B215TE	192-11-115L	FB115C	192-31-208G	FC208T	291-21-107	EP2B107TE	292-11-203L	EFB203C	292-31-215G	FC215T
191-21-215G	P2B215TE	192-11-203	FB203T	192-31-208L	FC208C	291-21-107G	EP2B107TE	292-11-207	EFB207T	292-31-215L	FC215C
191-21-215L	P2B215CE	192-11-203G	FB203T	192-31-211	FC211T	291-21-107L	EP2B107CE	292-11-207G	EFB207T	292-31-307	FC307T
191-21-307	P2B307TE	192-11-203L	FB203C	192-31-211G	FC211T	291-21-111	EP2B111TE	292-11-207L	EFB207C	292-31-307G	FC307T
191-21-307G	P2B307TE	192-11-207	FB207T	192-31-211L	FC211C	291-21-111G	EP2B111TE	292-11-208	EFB208T	292-31-307L	FC307C
191-21-307L	P2B307CE	192-11-207G	FB207T	192-31-215	FC215T	291-21-111L	EP2B111CE	292-11-208G	EFB208T	292-31-308	FC308T
191-21-308	P2B308TE	192-11-207L	FB207C	192-31-215G	FC215T	291-21-115	EP2B115TE	292-11-208L	EFB208C	292-31-308G	FC308T
191-21-308G	P2B308TE	192-11-208	FB208T	192-31-215L	FC215C	291-21-115G	EP2B115TE	292-11-211	EFB211T	292-31-308L	FC308C
191-21-308L	P2B308CE	192-11-208G	FB208T	192-31-307	FC307T	291-21-115L	EP2B115CE	292-11-211G	EFB211T	292-31-315	FC315T
191-31-107	FC107TE	192-11-208L	FB208C	192-31-307G	FC307T	291-21-203	EP2B203TE	292-11-211L	EFB211C	292-31-315G	FC315T
191-31-107G	FC107TE	192-11-211	FB211T	192-31-307L	FC307C	291-21-203G	EP2B203TE	292-11-215	EFB215T	292-31-315L	FC315C
191-31-107L	FC107CE	192-11-211G	FB211T	192-31-308	FC308T	291-21-203L	EP2B203CE	292-11-215G	EFB215T		
191-31-111	FC111TE	192-11-211L	FB211C	192-31-308G	FC308T	291-21-207	EP2B207TE	292-11-215L	EFB215C		
191-31-111G	FC111TE	192-11-215	FB215T	192-31-308L	FC308C	291-21-207G	EP2B207TE	292-11-307	EFB307T		
191-31-111L	FC111CE	192-11-215G	FB215T	192-31-315	FC315T	291-21-207L	EP2B207CE	292-11-307G	EFB307T		
191-31-115	FC115TE	192-11-215L	FB215C	192-31-315G	FC315T	291-21-208	EP2B208TE	292-11-307L	EFB307C		
191-31-115G	FC115TE	192-11-307	FB307T	192-31-315L	FC315C	291-21-208G	EP2B208TE	292-11-308	EFB308T		

* Moline is believed to be the trademark and/or trade name of Moline Bearing Company and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

PTI®* — PT Select Interchange Guide

PTI	PT Select	PTI	PT Select	PTI	PT Select	PTI	PT Select
SR2FB4-107R3NE	FB107T	SR2FC-111SLNE	FC111C	SR2PB2-115TLNE	P2B115C	SR2PB4-315R3NE	P4B315T
SR2FB4-107R3XP	FB107TE	SR2FC-111SLXP	FC111CE	SR2PB2-115TLXP	P2B115CE	SR2PB4-315R3XP	P4B315TE
SR2FB4-107SLNE	FB107C	SR2FC-111TLNE	FC111C	SR2PB2-203R3NE	P2B203T	SR2PB4-315SLNE	P4B315C
SR2FB4-107SLXP	FB107CE	SR2FC-111TLXP	FC111CE	SR2PB2-203R3XP	P2B203TE	SR2PB4-315SLXP	P4B315CE
SR2FB4-107TLNE	FB107C	SR2FC-115R3NE	FC115T	SR2PB2-203SLNE	P2B203C	SR2PB4-315TLNE	P4B315C
SR2FB4-107TLXP	FB107CE	SR2FC-115R3XP	FC115TE	SR2PB2-203SLXP	P2B203CE	SR2PB4-315TLXP	P4B315CE
SR2FB4-111R3NE	FB111T	SR2FC-115SLNE	FC115C	SR2PB2-203TLNE	P2B203C	SREPB2-107R3NE	EP2B107T
SR2FB4-111R3XP	FB111TE	SR2FC-115SLXP	FC115CE	SR2PB2-203TLXP	P2B203CE	SREPB2-107R3XP	EP2B107TE
SR2FB4-111SLNE	FB111C	SR2FC-115TLNE	FC115C	SR2PB2-207R3NE	P2B207T	SREPB2-107SLNE	EP2B107C
SR2FB4-111SLXP	FB111CE	SR2FC-115TLXP	FC115CE	SR2PB2-207R3XP	P2B207TE	SREPB2-107SLXP	EP2B107CE
SR2FB4-111TLNE	FB111C	SR2FC-203R3NE	FC203T	SR2PB2-207SLNE	P2B207C	SREPB2-107TLNE	EP2B107C
SR2FB4-111TLXP	FB111CE	SR2FC-203R3XP	FC203TE	SR2PB2-207SLXP	P2B207CE	SREPB2-107TLXP	EP2B107CE
SR2FB4-115R3NE	FB115T	SR2FC-203SLNE	FC203C	SR2PB2-207TLNE	P2B207C	SREPB2-111R3NE	EP2B111T
SR2FB4-115R3XP	FB115TE	SR2FC-203SLXP	FC203CE	SR2PB2-207TLXP	P2B207CE	SR2PB2-111R3XP	EP2B111TE
SR2FB4-115SLNE	FB115C	SR2FC-203TLNE	FC203C	SR2PB2-208R3NE	P2B208T	SREPB2-111SLNE	EP2B111C
SR2FB4-115SLXP	FB115CE	SR2FC-203TLXP	FC203CE	SR2PB2-208R3XP	P2B208TE	SREPB2-111SLXP	EP2B111CE
SR2FB4-115TLNE	FB115C	SR2FC-207R3NE	FC207T	SR2PB2-208SLNE	P2B208C	SREPB2-111TLNE	EP2B111C
SR2FB4-115TLXP	FB115CE	SR2FC-207R3XP	FC207TE	SR2PB2-208SLXP	P2B208CE	SREPB2-111TLXP	EP2B111CE
SR2FB4-203R3NE	FB203T	SR2FC-207SLNE	FC207C	SR2PB2-208TLNE	P2B208C	SREPB2-115R3NE	EP2B115T
SR2FB4-203R3XP	FB203TE	SR2FC-207SLXP	FC207CE	SR2PB2-208TLXP	P2B208CE	SREPB2-115R3XP	EP2B115TE
SR2FB4-203SLNE	FB203C	SR2FC-207TLNE	FC207C	SR2PB2-211R3NE	P2B211T	SREPB2-115SLNE	EP2B115C
SR2FB4-203SLXP	FB203CE	SR2FC-207TLXP	FC207CE	SR2PB2-211R3XP	P2B211TE	SREPB2-115SLXP	EP2B115CE
SR2FB4-203TLNE	FB203C	SR2FC-208R3NE	FC208T	SR2PB2-211SLNE	P2B211C	SREPB2-115TLNE	EP2B115C
SR2FB4-203TLXP	FB203CE	SR2FC-208R3XP	FC208TE	SR2PB2-211SLXP	P2B211CE	SREPB2-115TLXP	EP2B115CE
SR2FB4-207R3NE	FB207T	SR2FC-208SLNE	FC208C	SR2PB2-211TLNE	P2B211C	SREPB2-203R3NE	EP2B203T
SR2FB4-207R3XP	FB207TE	SR2FC-208SLXP	FC208CE	SR2PB2-211TLXP	P2B211CE	SREPB2-203R3XP	EP2B203TE
SR2FB4-207SLNE	FB207C	SR2FC-208TLNE	FC208C	SR2PB2-215R3NE	P2B215T	SREPB2-203SLNE	EP2B203C
SR2FB4-207SLXP	FB207CE	SR2FC-208TLXP	FC208CE	SR2PB2-215R3XP	P2B215TE	SREPB2-203SLXP	EP2B203CE
SR2FB4-207TLNE	FB207C	SR2FC-211R3NE	FC211T	SR2PB2-215SLNE	P2B215C	SREPB2-203TLNE	EP2B203C
SR2FB4-207TLXP	FB207CE	SR2FC-211R3XP	FC211TE	SR2PB2-215SLXP	P2B215CE	SREPB2-203TLXP	EP2B203CE
SR2FB4-208R3NE	FB208T	SR2FC-211SLNE	FC211C	SR2PB2-215TLNE	P2B215C	SREPB2-207R3NE	EP2B207T
SR2FB4-208R3XP	FB208TE	SR2FC-211SLXP	FC211CE	SR2PB2-215TLXP	P2B215CE	SREPB2-207R3XP	EP2B207TE
SR2FB4-208SLNE	FB208C	SR2FC-211TLNE	FC211C	SR2PB2-307R3NE	P2B307T	SREPB2-207SLNE	EP2B207C
SR2FB4-208SLXP	FB208CE	SR2FC-211TLXP	FC211CE	SR2PB2-307R3XP	P2B307TE	SREPB2-207SLXP	EP2B207CE
SR2FB4-208TLNE	FB208C	SR2FC-215R3NE	FC215T	SR2PB2-307SLNE	P2B307C	SREPB2-207TLNE	EP2B207C
SR2FB4-208TLXP	FB208CE	SR2FC-215R3XP	FC215TE	SR2PB2-307SLXP	P2B307CE	SREPB2-207TLXP	EP2B207CE
SR2FB4-211R3NE	FB211T	SR2FC-215SLNE	FC215C	SR2PB2-307TLNE	P2B307C	SREPB2-208R3NE	EP2B208T
SR2FB4-211R3XP	FB211TE	SR2FC-215SLXP	FC215CE	SR2PB2-307TLXP	P2B307CE	SREPB2-208R3XP	EP2B208TE
SR2FB4-211SLNE	FB211C	SR2FC-215TLNE	FC215C	SR2PB2-308R3NE	P2B308T	SREPB2-208SLNE	EP2B208C
SR2FB4-211SLXP	FB211CE	SR2FC-215TLXP	FC215CE	SR2PB2-308R3XP	P2B308TE	SREPB2-208SLXP	EP2B208CE
SR2FB4-211TLNE	FB211C	SR2FC-307R3NE	FC307T	SR2PB2-308SLNE	P2B308C	SREPB2-208TLNE	EP2B208C
SR2FB4-211TLXP	FB211CE	SR2FC-307R3XP	FC307TE	SR2PB2-308SLXP	P2B308CE	SREPB2-208TLXP	EP2B208CE
SR2FB4-215R3NE	FB215T	SR2FC-307SLNE	FC307C	SR2PB2-308TLNE	P2B308C	SREPB2-211R3NE	EP2B211T
SR2FB4-215R3XP	FB215TE	SR2FC-307SLXP	FC307CE	SR2PB2-308TLXP	P2B308CE	SREPB2-211R3XP	EP2B211TE
SR2FB4-215SLNE	FB215C	SR2FC-307TLNE	FC307C	SR2PB2-315R3NE	P2B315T	SREPB2-211SLNE	EP2B211C
SR2FB4-215SLXP	FB215CE	SR2FC-307TLXP	FC307CE	SR2PB2-315R3XP	P2B315TE	SREPB2-211SLXP	EP2B211CE
SR2FB4-215TLNE	FB215C	SR2FC-308R3NE	FC308T	SR2PB2-315SLNE	P2B315C	SREPB2-211TLNE	EP2B211C
SR2FB4-215TLXP	FB215CE	SR2FC-308R3XP	FC308TE	SR2PB2-315SLXP	P2B315CE	SREPB2-211TLXP	EP2B211CE
SR2FB4-307R3NE	FB307T	SR2FC-308SLNE	FC308C	SR2PB2-315TLNE	P2B315C	SREPB2-215R3NE	EP2B215T
SR2FB4-307R3XP	FB307TE	SR2FC-308SLXP	FC308CE	SR2PB2-315TLXP	P2B315CE	SREPB2-215R3XP	EP2B215TE
SR2FB4-307SLNE	FB307C	SR2FC-308TLNE	FC308C	SR2PB4-211R3NE	P4B211T	SREPB2-215SLNE	EP2B215C
SR2FB4-307SLXP	FB307CE	SR2FC-308TLXP	FC308CE	SR2PB4-211R3XP	P4B211TE	SREPB2-215SLXP	EP2B215CE
SR2FB4-307TLNE	FB307C	SR2FC-315R3NE	FC315T	SR2PB4-211SLNE	P4B211C	SREPB2-215TLNE	EP2B215C
SR2FB4-307TLXP	FB307CE	SR2FC-315R3XP	FC315TE	SR2PB4-211SLXP	P4B211CE	SREPB2-215TLXP	EP2B215CE
SR2FB4-308R3NE	FB308T	SR2FC-315SLNE	FC315C	SR2PB4-211TLNE	P4B211C	SREPB2-215TLXP	EP2B215CE
SR2FB4-308R3XP	FB308TE	SR2FC-315SLXP	FC315CE	SR2PB4-211TLXP	P4B211CE	SREPB2-307R3NE	EP2B307T
SR2FB4-308SLNE	FB308C	SR2FC-315TLNE	FC315C	SR2PB4-215R3NE	P4B215T	SREPB2-307R3XP	EP2B307TE
SR2FB4-308SLXP	FB308CE	SR2FC-315TLXP	FC315CE	SR2PB4-215R3XP	P4B215TE	SREPB2-307SLNE	EP2B307C
SR2FB4-308TLNE	FB308C	SR2PB2-107R3NE	P2B107T	SR2PB4-215SLNE	P4B215C	SREPB2-307SLXP	EP2B307CE
SR2FB4-308TLXP	FB308CE	SR2PB2-107R3XP	P2B107TE	SR2PB4-215SLXP	P4B215CE	SREPB2-307TLNE	EP2B307C
SR2FB4-315R3NE	FB315T	SR2PB2-107SLNE	P2B107C	SR2PB4-215TLNE	P4B215C	SREPB2-307TLXP	EP2B307CE
SR2FB4-315R3XP	FB315TE	SR2PB2-107SLXP	P2B107CE	SR2PB4-215TLXP	P4B215CE	SREPB2-308R3NE	EP2B308T
SR2FB4-315SLNE	FB315C	SR2PB2-107TLNE	P2B107C	SR2PB4-215TLXP	P4B215CE	SREPB2-308R3XP	EP2B308TE
SR2FB4-315SLXP	FB315CE	SR2PB2-107TLXP	P2B107CE	SR2PB4-307R3NE	P4B307T	SREPB2-308SLNE	EP2B308C
SR2FB4-315TLNE	FB315C	SR2PB2-111R3NE	P2B111T	SR2PB4-307R3XP	P4B307TE	SREPB2-308SLXP	EP2B308CE
SR2FB4-315TLXP	FB315CE	SR2PB2-111R3XP	P2B111TE	SR2PB4-307SLNE	P4B307C	SREPB2-308TLNE	EP2B308C
SR2FC-107R3NE	FC107T	SR2PB2-111SLNE	P2B111C	SR2PB4-307SLXP	P4B307CE	SREPB2-308TLXP	EP2B308CE
SR2FC-107R3XP	FC107TE	SR2PB2-111SLXP	P2B111CE	SR2PB4-307TLNE	P4B307C		
SR2FC-107SLNE	FC107C	SR2PB2-111TLNE	P2B111C	SR2PB4-307TLXP	P4B307CE		
SR2FC-107SLXP	FC107CE	SR2PB2-111TLXP	P2B111CE	SR2PB4-308R3NE	P4B308T		
SR2FC-107TLNE	FC107C	SR2PB2-115R3NE	P2B115T	SR2PB4-308R3XP	P4B308TE		
SR2FC-107TLXP	FC107CE	SR2PB2-115R3XP	P2B115TE	SR2PB4-308SLNE	P4B308C		
SR2FC-111R3NE	FC111T	SR2PB2-115SLNE	P2B115C	SR2PB4-308SLXP	P4B308CE		
SR2FC-111R3XP	FC111TE	SR2PB2-115SLXP	P2B115CE	SR2PB4-308TLNE	P4B308C		
				SR2PB4-308TLXP	P4B308CE		

Dodge®* S2000 — PT Select Interchange Guide

Dodge S2000	PT Select
EF4BS2-107L	EFB107C
EF4BS2-107LE	EFB107CE
EF4BS2-107R	EFB107T
EF4BS2-107RE	EFB107TE
EF4BS2-111L	EFB111C
EF4BS2-111LE	EFB111CE
EF4BS2-111R	EFB111T
EF4BS2-111RE	EFB111TE
EF4BS2-115L	EFB115C
EF4BS2-115LE	EFB115CE
EF4BS2-115R	EFB115T
EF4BS2-115RE	EFB115TE
EF4BS2-203L	EFB203C
EF4BS2-203LE	EFB203CE
EF4BS2-203R	EFB203T
EF4BS2-203RE	EFB203TE
EF4BS2-207L	EFB207C
EF4BS2-207LE	EFB207CE
EF4BS2-207R	EFB207T
EF4BS2-207RE	EFB207TE
EF4BS2-211L	EFB211C
EF4BS2-211LE	EFB211CE
EF4BS2-211R	EFB211T
EF4BS2-211RE	EFB211TE
EF4BS2-215L	EFB215C
EF4BS2-215LE	EFB215CE
EF4BS2-215R	EFB215T
EF4BS2-215RE	EFB215TE
EF4BS2-307L	EFB307C
EF4BS2-307LE	EFB307CE
EF4BS2-307R	EFB307T
EF4BS2-307RE	EFB307TE
EF4BS2-315L	EFB315C
EF4BS2-315LE	EFB315CE
EF4BS2-315R	EFB315T
EF4BS2-315RE	EFB315TE
EP2BS2-107L	EP2B107C
EP2BS2-107LE	EP2B107CE
EP2BS2-107R	EP2B107T
EP2BS2-107RE	EP2B107TE
EP2BS2-111L	EP2B111C
EP2BS2-111LE	EP2B111CE
EP2BS2-111R	EP2B111T
EP2BS2-111RE	EP2B111TE
EP2BS2-115L	EP2B115C
EP2BS2-115LE	EP2B115CE
EP2BS2-115R	EP2B115T
EP2BS2-115RE	EP2B115TE
EP2BS2-203L	EP2B203C
EP2BS2-203LE	EP2B203CE
EP2BS2-203R	EP2B203T
EP2BS2-203RE	EP2B203TE
EP2BS2-207L	EP2B207C
EP2BS2-207LE	EP2B207CE
EP2BS2-207R	EP2B207T
EP2BS2-207RE	EP2B207TE
EP2BS2-211L	EP2B211C
EP2BS2-211LE	EP2B211CE
EP2BS2-211R	EP2B211T
EP2BS2-211RE	EP2B211TE
EP2BS2-215L	EP2B215C
EP2BS2-215LE	EP2B215CE
EP2BS2-215R	EP2B215T
EP2BS2-215RE	EP2B215TE

Dodge S2000	PT Select
EP2BS2-215RE	EP2B215TE
EP2BS2-307L	EP2B307C
EP2BS2-307LE	EP2B307CE
EP2BS2-307R	EP2B307T
EP2BS2-307RE	EP2B307TE
F4BUN2-107	FB107T
F4BUN2-107E	FB107TE
F4BUN2-111	FB111T
F4BUN2-111E	FB111TE
F4BUN2-115	FB115T
F4BUN2-115E	FB115TE
F4BUN2-203	FB203T
F4BUN2-203E	FB203TE
F4BUN2-207	FB207T
F4BUN2-207E	FB207TE
F4BUN2-208	FB208T
F4BUN2-208E	FB208TE
F4BUN2-211	FB211T
F4BUN2-211E	FB211TE
F4BUN2-215	FB215T
F4BUN2-215E	FB215TE
F4BUN2-307	FB307T
F4BUN2-307E	FB307TE
F4BUN2-308	FB308T
F4BUN2-308E	FB308TE
F4BUN2-315	FB315T
F4BUN2-315E	FB315TE
F4SS2-107L	FB107C
F4SS2-107LE	FB107CE
F4SS2-107R	FB107T
F4SS2-107RE	FB107TE
F4SS2-111L	FB111C
F4SS2-111LE	FB111CE
F4SS2-111R	FB111T
F4SS2-111RE	FB111TE
F4SS2-115L	FB115C
F4SS2-115LE	FB115CE
F4SS2-115R	FB115T
F4SS2-115RE	FB115TE
F4SS2-203L	FB203C
F4SS2-203LE	FB203CE
F4SS2-203R	FB203T
F4SS2-203RE	FB203TE
F4SS2-207L	FB207C
F4SS2-207LE	FB207CE
F4SS2-207R	FB207T
F4SS2-207RE	FB207TE
F4SS2-211L	FB211C
F4SS2-211LE	FB211CE
F4SS2-211R	FB211T
F4SS2-211RE	FB211TE
F4SS2-215L	FB215C
F4SS2-215LE	FB215CE
F4SS2-215R	FB215T
F4SS2-215RE	FB215TE
F4SS2-307L	FB307C
F4SS2-307LE	FB307CE
F4SS2-307R	FB307T
F4SS2-307RE	FB307TE
F4SS2-315L	FB315C
F4SS2-315LE	FB315CE
F4SS2-315R	FB315T
F4SS2-315RE	FB315TE

Dodge S2000	PT Select
FCS2-107L	FC107C
FCS2-107LE	FC107CE
FCS2-107R	FC107T
FCS2-107RE	FC107TE
FCS2-111L	FC111C
FCS2-111LE	FC111CE
FCS2-111R	FC111T
FCS2-111RE	FC111TE
FCS2-115L	FC115C
FCS2-115LE	FC115CE
FCS2-115R	FC115T
FCS2-115RE	FC115TE
FCS2-203L	FC203C
FCS2-203LE	FC203CE
FCS2-203R	FC203T
FCS2-203RE	FC203TE
FCS2-207L	FC207C
FCS2-207LE	FC207CE
FCS2-207R	FC207T
FCS2-207RE	FC207TE
FCS2-211L	FC211C
FCS2-211LE	FC211CE
FCS2-211R	FC211T
FCS2-211RE	FC211TE
FCS2-215L	FC215C
FCS2-215LE	FC215CE
FCS2-215R	FC215T
FCS2-215RE	FC215TE
FCS2-307L	FC307C
FCS2-307LE	FC307CE
FCS2-307R	FC307T
FCS2-307RE	FC307TE
FCS2-315L	FC315C
FCS2-315LE	FC315CE
FCS2-315R	FC315T
FCS2-315RE	FC315TE
P2BS2-107L	P2B107C
P2BS2-107LE	P2B107CE
P2BS2-107R	P2B107T
P2BS2-107RE	P2B107TE
P2BS2-111L	P2B111C
P2BS2-111LE	P2B111CE
P2BS2-111R	P2B111T
P2BS2-111RE	P2B111TE
P2BS2-115L	P2B115C
P2BS2-115LE	P2B115CE
P2BS2-115R	P2B115T
P2BS2-115RE	P2B115TE
P2BS2-203L	P2B203C
P2BS2-203LE	P2B203CE
P2BS2-203R	P2B203T
P2BS2-203RE	P2B203TE
P2BS2-207L	P2B207C
P2BS2-207LE	P2B207CE
P2BS2-207R	P2B207T
P2BS2-207RE	P2B207TE
P2BS2-211L	P2B211C
P2BS2-211LE	P2B211CE
P2BS2-211R	P2B211T
P2BS2-211RE	P2B211TE
P2BS2-215L	P2B215C
P2BS2-215LE	P2B215CE
P2BS2-215R	P2B215T
P2BS2-215RE	P2B215TE

Dodge S2000	PT Select
P2BS2-215RE	P2B215TE
P2BS2-307L	P2B307C
P2BS2-307LE	P2B307CE
P2BS2-307R	P2B307T
P2BS2-307RE	P2B307TE
P2BS2-315L	P2B315C
P2BS2-315LE	P2B315CE
P2BS2-315R	P2B315T
P2BS2-315RE	P2B315TE
P4BS2-115L	P4B115C
P4BS2-115LE	P4B115CE
P4BS2-115R	P4B115T
P4BS2-115RE	P4B115TE
P4BS2-203L	P4B203C
P4BS2-203LE	P4B203CE
P4BS2-203R	P4B203T
P4BS2-203RE	P4B203TE
P4BS2-207L	P4B207C
P4BS2-207LE	P4B207CE
P4BS2-207R	P4B207T
P4BS2-207RE	P4B207TE
P4BS2-211L	P4B211C
P4BS2-211LE	P4B211CE
P4BS2-211R	P4B211T
P4BS2-211RE	P4B211TE
P4BS2-215L	P4B215C
P4BS2-215LE	P4B215CE
P4BS2-215R	P4B215T
P4BS2-215RE	P4B215TE
P4BS2-307L	P4B307C
P4BS2-307LE	P4B307CE
P4BS2-307R	P4B307T
P4BS2-307RE	P4B307TE
P4BS2-315L	P4B315C
P4BS2-315LE	P4B315CE
P4BS2-315R	P4B315T
P4BS2-315RE	P4B315TE

* Dodge is believed to be the trademark and/or trade name of Dodge Industrial, Inc. and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

Dodge®* Catalog – PT Select Interchange Guide

Dodge Catalog	PT Select	Dodge Catalog	PT Select	Dodge Catalog	PT Select	Dodge Catalog	PT Select
048034	FB107T	070371	P4B307T	070681	FC207TE	071432	EP2B307CE
048036	FB111T	070373	P4B315T	070683	FC211TE	071470	EFB107T
048038	FB115T	070379	P4B115TE	070684	FC215TE	071471	EFB111T
048040	FB203T	070381	P4B203TE	070687	FC307TE	071472	EFB115T
048041	FB207T	070383	P4B207TE	070689	FC315TE	071474	EFB203T
048042	FB208T	070385	P4B211TE	070699	FC107C	071475	EFB207T
048043	FB211T	070386	P4B215TE	070702	FC111C	071476	EFB211T
048045	FB215T	070389	P4B307TE	070704	FC115C	071477	EFB215T
048047	FB307T	070391	P4B315TE	070706	FC203C	071479	EFB307T
048048	FB308T	070397	P4B115C	070708	FC207C	071480	EFB315T
048049	FB315T	070399	P4B203C	070710	FC211C	071483	EFB107TE
048051	FB107TE	070401	P4B207C	070711	FC215C	071484	EFB111TE
048053	FB111TE	070403	P4B211C	070714	FC307C	071485	EFB115TE
048055	FB115TE	070404	P4B215C	070716	FC315C	071487	EFB203TE
048057	FB203TE	070407	P4B307C	070726	FC107CE	071488	EFB207TE
048058	FB207TE	070409	P4B315C	070729	FC111CE	071489	EFB211TE
048059	FB208TE	070415	P4B115CE	070731	FC115CE	071490	EFB215TE
048060	FB211TE	070417	P4B203CE	070733	FC203CE	071492	EFB307TE
048062	FB215TE	070419	P4B207CE	070735	FC207CE	071493	EFB315TE
048064	FB307TE	070421	P4B211CE	070737	FC211CE	071496	EFB107C
048065	FB308TE	070422	P4B215CE	070738	FC215CE	071497	EFB111C
048066	FB315TE	070425	P4B307CE	070741	FC307CE	071498	EFB115C
070273	P2B107T	070427	P4B315CE	070743	FC315CE	071500	EFB203C
070276	P2B111T	070542	FB107T	070854	FB107CE	071501	EFB207C
070278	P2B115T	070545	FB111T	070857	FB111CE	071502	EFB211C
070280	P2B203T	070547	FB115T	070859	FB115CE	071503	EFB215C
070282	P2B207T	070549	FB203T	070861	FB203CE	071505	EFB307C
070284	P2B211T	070551	FB207T	070863	FB207CE	071506	EFB315C
070285	P2B215T	070553	FB211T	070865	FB211CE	071509	EFB107CE
070288	P2B307T	070554	FB215T	070866	FB215CE	071510	EFB111CE
070290	P2B315T	070557	FB307T	070869	FB307CE	071511	EFB115CE
070296	P2B107TE	070559	FB315T	070871	FB315CE	071513	EFB203CE
070299	P2B111TE	070565	FB107TE	071390	EP2B107T	071514	EFB207CE
070301	P2B115TE	070568	FB111TE	071391	EP2B111T	071515	EFB211CE
070303	P2B203TE	070570	FB115TE	071392	EP2B115T	071516	EFB215CE
070305	P2B207TE	070572	FB203TE	071394	EP2B203T	071518	EFB307CE
070307	P2B211TE	070574	FB207TE	071395	EP2B207T	071519	EFB315CE
070308	P2B215TE	070576	FB211TE	071396	EP2B211T		
070311	P2B307TE	070577	FB215TE	071397	EP2B215T		
070313	P2B315TE	070580	FB307TE	071399	EP2B307T		
070319	P2B107C	070582	FB315TE	071401	EP2B107TE		
070322	P2B111C	070601	FB107C	071402	EP2B111TE		
070324	P2B115C	070604	FB111C	071403	EP2B115TE		
070326	P2B203C	070606	FB115C	071405	EP2B203TE		
070328	P2B207C	070608	FB203C	071406	EP2B207TE		
070330	P2B211C	070610	FB207C	071407	EP2B211TE		
070331	P2B215C	070612	FB211C	071408	EP2B215TE		
070334	P2B307C	070613	FB215C	071410	EP2B307TE		
070336	P2B315C	070616	FB307C	071412	EP2B107C		
070342	P2B107CE	070618	FB315C	071413	EP2B111C		
070345	P2B111CE	070645	FC107T	071414	EP2B115C		
070347	P2B115CE	070648	FC111T	071416	EP2B203C		
070349	P2B203CE	070650	FC115T	071417	EP2B207C		
070351	P2B207CE	070652	FC203T	071418	EP2B211C		
070353	P2B211CE	070654	FC207T	071419	EP2B215C		
070354	P2B215CE	070656	FC211T	071421	EP2B307C		
070357	P2B307CE	070657	FC215T	071423	EP2B107CE		
070359	P2B315CE	070660	FC307T	071424	EP2B111CE		
070361	P4B115T	070662	FC315T	071425	EP2B115CE		
070363	P4B203T	070672	FC107TE	071427	EP2B203CE		
070365	P4B207T	070675	FC111TE	071428	EP2B207CE		
070367	P4B211T	070677	FC115TE	071429	EP2B211CE		
070368	P4B215T	070679	FC203TE	071430	EP2B215CE		

Timken-QM* — PT Select Interchange Guide


Timken-QM	PT Select	Timken-QM	PT Select	Timken-QM	PT Select	Timken-QM	PT Select
QAC08A-107SEM	FC107TE	QACW15A-215SEM	FC215TE	QAFL11A-203SEM	FB203TE	QAPF13A-207SEM	P4B207TE
QAC08A-107SET	FC107CE	QACW15A-215SET	FC215CE	QAFL11A-203SET	FB203CE	QAPF13A-207SET	P4B207CE
QAC08A-107SM	FC107T	QACW15A-215SM	FC215T	QAFL11A-203SM	FB203T	QAPF13A-207SM	P4B207T
QAC08A-107ST	FC107C	QACW15A-215ST	FC215C	QAFL11A-203ST	FB203C	QAPF13A-207ST	P4B207C
QAC09A-111SEM	FC111TE	QACW18A-307SEM	FC307TE	QAFL13A-207SEM	FB207TE	QAPF13A-208SEM	P4B208TE
QAC09A-111SET	FC111CE	QACW18A-307SET	FC307CE	QAFL13A-207SET	FB207CE	QAPF13A-208SET	P4B208CE
QAC09A-111SM	FC111T	QACW18A-307SM	FC307T	QAFL13A-207SM	FB207T	QAPF13A-208SM	P4B208T
QAC09A-111ST	FC111C	QACW18A-307ST	FC307C	QAFL13A-207ST	FB207C	QAPF13A-208ST	P4B208C
QAC10A-115SEM	FC115TE	QACW18A-308SEM	FC308TE	QAFL13A-208SEM	FB208TE	QAPF15A-211SEM	P4B211TE
QAC10A-115SET	FC115CE	QACW18A-308SET	FC308CE	QAFL13A-208SET	FB208CE	QAPF15A-211SET	P4B211CE
QAC10A-115SM	FC115T	QACW18A-308SM	FC308T	QAFL13A-208SM	FB208T	QAPF15A-211SM	P4B211T
QAC10A-115ST	FC115C	QACW18A-308ST	FC308C	QAFL13A-208ST	FB208C	QAPF15A-211ST	P4B211C
QAC11A-203SEM	FC203TE	QACW20A-315SEM	FC315TE	QAFL15A-211SEM	FB211TE	QAPF15A-215SEM	P4B215TE
QAC11A-203SET	FC203CE	QACW20A-315SET	FC315CE	QAFL15A-211SET	FB211CE	QAPF15A-215SET	P4B215CE
QAC11A-203SM	FC203T	QACW20A-315SM	FC315T	QAFL15A-211SM	FB211T	QAPF15A-215SM	P4B215T
QAC11A-203ST	FC203C	QACW20A-315ST	FC315C	QAFL15A-211ST	FB211C	QAPF15A-215ST	P4B215C
QAC13A-207SEM	FC207TE	QAF08A-107SEM	EFB107TE	QAFL15A-215SEM	FB215TE	QAPF18A-307SEM	P4B307TE
QAC13A-207SET	FC207CE	QAF08A-107SET	EFB107CE	QAFL15A-215SET	FB215CE	QAPF18A-307SET	P4B307CE
QAC13A-207SM	FC207T	QAF08A-107SM	EFB107T	QAFL15A-215SM	FB215T	QAPF18A-307SM	P4B307T
QAC13A-207ST	FC207C	QAF08A-107ST	EFB107C	QAFL15A-215ST	FB215C	QAPF18A-307ST	P4B307C
QAC13A-208SEM	FC208TE	QAF09A-111SEM	EFB111TE	QAFL18A-307SEM	FB307TE	QAPF18A-308SEM	P4B308TE
QAC13A-208SET	FC208CE	QAF09A-111SET	EFB111CE	QAFL18A-307SET	FB307CE	QAPF18A-308SET	P4B308CE
QAC13A-208SM	FC208T	QAF09A-111SM	EFB111T	QAFL18A-307SM	FB307T	QAPF18A-308SM	P4B308T
QAC13A-208ST	FC208C	QAF09A-111ST	EFB111C	QAFL18A-307ST	FB307C	QAPF18A-308ST	P4B308C
QAC15A-211SEM	FC211TE	QAF10A-115SEM	EFB115TE	QAFL18A-308SEM	FB308TE	QAPF20A-315SEM	P4B315TE
QAC15A-211SET	FC211CE	QAF10A-115SET	EFB115CE	QAFL18A-308SET	FB308CE	QAPF20A-315SET	P4B315CE
QAC15A-211SM	FC211T	QAF10A-115SM	EFB115T	QAFL18A-308SM	FB308T	QAPF20A-315SM	P4B315T
QAC15A-211ST	FC211C	QAF10A-115ST	EFB115C	QAFL18A-308ST	FB308C	QAPF20A-315ST	P4B315C
QAC15A-215SEM	FC215TE	QAF11A-203SEM	EFB203TE	QAFL20A-315SEM	FB315TE	QAPL08A-107SEM	P2B107TE
QAC15A-215SET	FC215CE	QAF11A-203SET	EFB203CE	QAFL20A-315SET	FB315CE	QAPL08A-107SET	P2B107CE
QAC15A-215SM	FC215T	QAF11A-203SM	EFB203T	QAFL20A-315SM	FB315T	QAPL08A-107SM	P2B107T
QAC15A-215ST	FC215C	QAF11A-203ST	EFB203C	QAFL20A-315ST	FB315C	QAPL08A-107ST	P2B107C
QAC18A-307SEM	FC307TE	QAF13A-207SEM	EFB207TE	QAP08A-107SEM	EP2B107TE	QAPL09A-111SEM	P2B111TE
QAC18A-307SET	FC307CE	QAF13A-207SET	EFB207CE	QAP08A-107SET	EP2B107CE	QAPL09A-111SET	P2B111CE
QAC18A-307SM	FC307T	QAF13A-207SM	EFB207T	QAP08A-107SM	EP2B107T	QAPL09A-111SM	P2B111T
QAC18A-307ST	FC307C	QAF13A-207ST	EFB207C	QAP08A-107ST	EP2B107C	QAPL09A-111ST	P2B111C
QAC18A-308SEM	FC308TE	QAF13A-208SEM	EFB208TE	QAP09A-111SEM	EP2B111TE	QAPL10A-115SEM	P2B115TE
QAC18A-308SET	FC308CE	QAF13A-208SET	EFB208CE	QAP09A-111SET	EP2B111CE	QAPL10A-115SET	P2B115CE
QAC18A-308SM	FC308T	QAF13A-208SM	EFB208T	QAP09A-111SM	EP2B111T	QAPL10A-115SM	P2B115T
QAC18A-308ST	FC308C	QAF13A-208ST	EFB208C	QAP09A-111ST	EP2B111C	QAPL10A-115ST	P2B115C
QAC20A-315SEM	FC315TE	QAF15A-211SEM	EFB211TE	QAP10A-115SEM	EP2B115TE	QAPL11A-203SEM	P2B203TE
QAC20A-315SET	FC315CE	QAF15A-211SET	EFB211CE	QAP10A-115SET	EP2B115CE	QAPL11A-203SET	P2B203CE
QAC20A-315SM	FC315T	QAF15A-211SM	EFB211T	QAP10A-115SM	EP2B115T	QAPL11A-203SM	P2B203T
QAC20A-315ST	FC315C	QAF15A-211ST	EFB211C	QAP10A-115ST	EP2B115C	QAPL11A-203ST	P2B203C
QACW08A-107SEM	FC107TE	QAF15A-215SEM	EFB215TE	QAP11A-203SEM	EP2B203TE	QAPL13A-207SEM	P2B207TE
QACW08A-107SET	FC107CE	QAF15A-215SET	EFB215CE	QAP11A-203SET	EP2B203CE	QAPL13A-207SET	P2B207CE
QACW08A-107SM	FC107T	QAF15A-215SM	EFB215T	QAP11A-203SM	EP2B203T	QAPL13A-207SM	P2B207T
QACW08A-107ST	FC107C	QAF15A-215ST	EFB215C	QAP11A-203ST	EP2B203C	QAPL13A-207ST	P2B207C
QACW09A-111SEM	FC111TE	QAF18A-307SEM	EFB307TE	QAP13A-207SEM	EP2B207TE	QAPL13A-208SEM	P2B208TE
QACW09A-111SET	FC111CE	QAF18A-307SET	EFB307CE	QAP13A-207SET	EP2B207CE	QAPL13A-208SET	P2B208CE
QACW09A-111SM	FC111T	QAF18A-307SM	EFB307T	QAP13A-207SM	EP2B207T	QAPL13A-208SM	P2B208T
QACW09A-111ST	FC111C	QAF18A-307ST	EFB307C	QAP13A-207ST	EP2B207C	QAPL13A-208ST	P2B208C
QACW10A-115SEM	FC115TE	QAF18A-308SEM	EFB308TE	QAP13A-208SEM	EP2B208TE	QAPL15A-211SEM	P2B211TE
QACW10A-115SET	FC115CE	QAF18A-308SET	EFB308CE	QAP13A-208SET	EP2B208CE	QAPL15A-211SET	P2B211CE
QACW10A-115SM	FC115T	QAF18A-308SM	EFB308T	QAP13A-208SM	EP2B208T	QAPL15A-211SM	P2B211T
QACW10A-115ST	FC115C	QAF18A-308ST	EFB308C	QAP13A-208ST	EP2B208C	QAPL15A-211ST	P2B211C
QACW11A-203SEM	FC203TE	QAF20A-315SEM	EFB315TE	QAP15A-211SEM	EP2B211TE	QAPL15A-215SEM	P2B215TE
QACW11A-203SET	FC203CE	QAF20A-315SET	EFB315CE	QAP15A-211SET	EP2B211CE	QAPL15A-215SET	P2B215CE
QACW11A-203SM	FC203T	QAF20A-315SM	EFB315T	QAP15A-211SM	EP2B211T	QAPL15A-215SM	P2B215T
QACW11A-203ST	FC203C	QAF20A-315ST	EFB315C	QAP15A-211ST	EP2B211C	QAPL15A-215ST	P2B215C
QACW13A-207SEM	FC207TE	QAFLO8A-107SEM	FB107TE	QAP15A-215SEM	EP2B215TE	QAPL18A-307SEM	P2B307TE
QACW13A-207SET	FC207CE	QAFLO8A-107SET	FB107CE	QAP15A-215SET	EP2B215CE	QAPL18A-307SET	P2B307CE
QACW13A-207SM	FC207T	QAFLO8A-107SM	FB107T	QAP15A-215SM	EP2B215T	QAPL18A-307SM	P2B307T
QACW13A-207ST	FC207C	QAFLO8A-107ST	FB107C	QAP15A-215ST	EP2B215C	QAPL18A-307ST	P2B307C
QACW13A-208SEM	FC208TE	QAFLO9A-111SEM	FB111TE	QAP18A-307SEM	EP2B307TE	QAPL18A-308SEM	P2B308TE
QACW13A-208SET	FC208CE	QAFLO9A-111SET	FB111CE	QAP18A-307SET	EP2B307CE	QAPL18A-308SET	P2B308CE
QACW13A-208SM	FC208T	QAFLO9A-111SM	FB111T	QAP18A-307SM	EP2B307T	QAPL18A-308SM	P2B308T
QACW13A-208ST	FC208C	QAFLO9A-111ST	FB111C	QAP18A-307ST	EP2B307C	QAPL18A-308ST	P2B308C
QACW15A-211SEM	FC211TE	QAFL10A-115SEM	FB115TE	QAP18A-308SEM	EP2B308TE	QAPL20A-315SEM	P2B315TE
QACW15A-211SET	FC211CE	QAFL10A-115SET	FB115CE	QAP18A-308SET	EP2B308CE	QAPL20A-315SET	P2B315CE
QACW15A-211SM	FC211T	QAFL10A-115SM	FB115T	QAP18A-308SM	EP2B308T	QAPL20A-315SM	P2B315T
QACW15A-211ST	FC211C	QAFL10A-115ST	FB115C	QAP18A-308ST	EP2B308C	QAPL20A-315ST	P2B315C

* Timken-QM is believed to be the trademark and/or trade name of The Timken Company and is not owned or controlled by Regal Rexnord Corporation or its affiliates.

Sealmaster — PT Select Interchange Guide

Sealmaster	PT Select	Sealmaster	PT Select	Sealmaster	PT Select	Sealmaster	PT Select
USFB5000-107	FB107C	USFBE5000E-207C	EFB207TE	USFCE5000-215	FC215C	USRBE5000-115C	EP2B115T
USFB5000-107C	FB107T	USFBE5000E-208	EFB208CE	USFCE5000-215C	FC215T	USRBE5000-203	EP2B203C
USFB5000-111	FB111C	USFBE5000E-208C	EFB208TE	USFCE5000-307	FC307C	USRBE5000-203C	EP2B203T
USFB5000-111C	FB111T	USFBE5000E-211	EFB211CE	USFCE5000-307C	FC307T	USRBE5000-207	EP2B207C
USFB5000-115	FB115C	USFBE5000E-211C	EFB211TE	USFCE5000-308	FC308C	USRBE5000-207C	EP2B207T
USFB5000-115C	FB115T	USFBE5000E-215	EFB215CE	USFCE5000-308C	FC308T	USRBE5000-208	EP2B208C
USFB5000-203	FB203C	USFBE5000E-215C	EFB215TE	USFCE5000-315	FC315C	USRBE5000-208C	EP2B208T
USFB5000-203C	FB203T	USFBE5000E-307	EFB307CE	USFCE5000-315C	FC315T	USRBE5000-211	EP2B211C
USFB5000-207	FB207C	USFBE5000E-307C	EFB307TE	USFCE5000-115	FC115CE	USRBE5000-211C	EP2B211T
USFB5000-207C	FB207T	USFBE5000E-308	EFB308CE	USFCE5000E-115C	FC115TE	USRBE5000-215	EP2B215C
USFB5000-208	FB208C	USFBE5000E-308C	EFB308TE	USFCE5000E-203	FC203CE	USRBE5000-215C	EP2B215T
USFB5000-208C	FB208T	USFBE5000E-315	EFB315CE	USFCE5000E-203C	FC203TE	USRBE5000-307	EP2B307C
USFB5000-211	FB211C	USFBE5000E-315C	EFB315TE	USFCE5000E-207	FC207CE	USRBE5000-307C	EP2B307T
USFB5000-211C	FB211T	USFC5000-107	FC107C	USFCE5000E-207C	FC207TE	USRBE5000-308	EP2B308C
USFB5000-215	FB215C	USFC5000-107C	FC107T	USFCE5000E-208	FC208CE	USRBE5000-308C	EP2B308T
USFB5000-215C	FB215T	USFC5000-111	FC111C	USFCE5000E-208C	FC208TE	USRBE5000E-115	EP2B115CE
USFB5000-307	FB307C	USFC5000-111C	FC111T	USFCE5000E-211	FC211CE	USRBE5000E-115C	EP2B115TE
USFB5000-307C	FB307T	USFC5000-115	FC115C	USFCE5000E-211C	FC211TE	USRBE5000E-203	EP2B203CE
USFB5000-308	FB308C	USFC5000-115C	FC115T	USFCE5000E-215	FC215CE	USRBE5000E-203C	EP2B203TE
USFB5000-308C	FB308T	USFC5000-203	FC203C	USFCE5000E-215C	FC215TE	USRBE5000E-207	EP2B207CE
USFB5000-315	FB315C	USFC5000-203C	FC203T	USFCE5000E-307	FC307CE	USRBE5000E-207C	EP2B207TE
USFB5000-315C	FB315T	USFC5000-207	FC207C	USFCE5000E-307C	FC307TE	USRBE5000E-208	EP2B208CE
USFB5000E-107	FB107CE	USFC5000-207C	FC207T	USFCE5000E-308	FC308CE	USRBE5000E-208C	EP2B208TE
USFB5000E-107C	FB107TE	USFC5000-208	FC208C	USFCE5000E-308C	FC308TE	USRBE5000E-211	EP2B211CE
USFB5000E-111	FB111CE	USFC5000-208C	FC208T	USFCE5000E-315	FC315CE	USRBE5000E-211C	EP2B211TE
USFB5000E-111C	FB111TE	USFC5000-211	FC211C	USFCE5000E-315C	FC315TE	USRBE5000E-215	EP2B215CE
USFB5000E-115	FB115CE	USFC5000-211C	FC211T	USRB5000-107	P2B107C	USRBE5000E-215C	EP2B215TE
USFB5000E-115C	FB115TE	USFC5000-215	FC215C	USRB5000-107C	P2B107T	USRBE5000E-307	EP2B307CE
USFB5000E-203	FB203CE	USFC5000-215C	FC215T	USRB5000-111	P2B111C	USRBE5000E-307C	EP2B307TE
USFB5000E-203C	FB203TE	USFC5000-307	FC307C	USRB5000-111C	P2B111T	USRBE5000E-308	EP2B308CE
USFB5000E-207	FB207CE	USFC5000-307C	FC307T	USRB5000-115	P2B115C	USRBE5000E-308C	EP2B308TE
USFB5000E-207C	FB207TE	USFC5000-308	FC308C	USRB5000-115C	P2B115T	USRBF5000-207	P4B207C
USFB5000E-208	FB208CE	USFC5000-308C	FC308T	USRB5000-203	P2B203C	USRBF5000-207C	P4B207T
USFB5000E-208C	FB208TE	USFC5000-315	FC315C	USRB5000-203C	P2B203T	USRBF5000-208	P4B208C
USFB5000E-211	FB211CE	USFC5000-315C	FC315T	USRB5000-207	P2B207C	USRBF5000-208C	P4B208T
USFB5000E-211C	FB211TE	USFC5000E-107	FC107CE	USRB5000-207C	P2B207T	USRBF5000-211	P4B211C
USFB5000E-215	FB215CE	USFC5000E-107C	FC107TE	USRB5000-208	P2B208C	USRBF5000-211C	P4B211T
USFB5000E-215C	FB215TE	USFC5000E-111	FC111CE	USRB5000-208C	P2B208T	USRBF5000-215	P4B215C
USFB5000E-307	FB307CE	USFC5000E-111C	FC111TE	USRB5000-211	P2B211C	USRBF5000-215C	P4B215T
USFB5000E-307C	FB307TE	USFC5000E-115	FC115CE	USRB5000-211C	P2B211T	USRBF5000-307	P4B307C
USFB5000E-308	FB308CE	USFC5000E-115C	FC115TE	USRB5000-215	P2B215C	USRBF5000-307C	P4B307T
USFB5000E-308C	FB308TE	USFC5000E-203	FC203CE	USRB5000-215C	P2B215T	USRBF5000-308	P4B308C
USFB5000E-315	FB315CE	USFC5000E-203C	FC203TE	USRB5000-307	P2B307C	USRBF5000-308C	P4B308T
USFB5000E-315C	FB315TE	USFC5000E-207	FC207CE	USRB5000-307C	P2B307T	USRBF5000-315	P4B315C
USFB5000-115	EFB115C	USFC5000E-207C	FC207TE	USRB5000-308	P2B308C	USRBF5000-315C	P4B315T
USFBE5000-115C	EFB115T	USFC5000E-208	FC208CE	USRB5000-308C	P2B308T	USRBF5000E-207	P4B207CE
USFBE5000-203	EFB203C	USFC5000E-208C	FC208TE	USRB5000E-107	P2B107CE	USRBF5000E-207C	P4B207TE
USFBE5000-203C	EFB203T	USFC5000E-211	FC211CE	USRB5000E-107C	P2B107TE	USRBF5000E-208	P4B208CE
USFBE5000-207	EFB207C	USFC5000E-211C	FC211TE	USRB5000E-111	P2B111CE	USRBF5000E-208C	P4B208TE
USFBE5000-207C	EFB207T	USFC5000E-215	FC215CE	USRB5000E-111C	P2B111TE	USRBF5000E-211	P4B211CE
USFBE5000-208	EFB208C	USFC5000E-215C	FC215TE	USRB5000E-115	P2B115CE	USRBF5000E-211C	P4B211TE
USFBE5000-208C	EFB208T	USFC5000E-307	FC307CE	USRB5000E-115C	P2B115TE	USRBF5000E-215	P4B215CE
USFBE5000-211	EFB211C	USFC5000E-307C	FC307TE	USRB5000E-203	P2B203CE	USRBF5000E-215C	P4B215TE
USFBE5000-211C	EFB211T	USFC5000E-308	FC308CE	USRB5000E-203C	P2B203TE	USRBF5000E-307	P4B307CE
USFBE5000-215	EFB215C	USFC5000E-308C	FC308TE	USRB5000E-207	P2B207CE	USRBF5000E-307C	P4B307TE
USFBE5000-215C	EFB215T	USFC5000E-315	FC315CE	USRB5000E-207C	P2B207TE	USRBF5000E-308	P4B308CE
USFBE5000-307	EFB307C	USFC5000E-315C	FC315TE	USRB5000E-208	P2B208CE	USRBF5000E-308C	P4B308TE
USFBE5000-307C	EFB307T	USFCE5000-115	FC115C	USRB5000E-208C	P2B208TE	USRBF5000E-315	P4B315CE
USFBE5000-308	EFB308C	USFCE5000-115C	FC115T	USRB5000E-211	P2B211CE	USRBF5000E-315C	P4B315TE
USFBE5000-308C	EFB308T	USFCE5000-203	FC203C	USRB5000E-211C	P2B211TE		
USFBE5000-315	EFB315C	USFCE5000-203C	FC203T	USRB5000E-215	P2B215CE		
USFBE5000-315C	EFB315T	USFCE5000-207	FC207C	USRB5000E-215C	P2B215TE		
USFBE5000E-115	EFB115CE	USFCE5000-207C	FC207T	USRB5000E-307	P2B307CE		
USFBE5000E-115C	EFB115TE	USFCE5000-208	FC208C	USRB5000E-307C	P2B307TE		
USFBE5000E-203	EFB203CE	USFCE5000-208C	FC208T	USRB5000E-308	P2B308CE		
USFBE5000E-203C	EFB203TE	USFCE5000-211	FC211C	USRB5000E-308C	P2B308TE		
USFBE5000E-207	EFB207CE	USFCE5000-211C	FC211T	USRBE5000-115	EP2B115C		

This Page Intentionally Left Blank



PT Select

Motion Control Solutions Regal Rexnord

Contact us: [regalrexnord.com/contact](https://www.regalrexnord.com/contact)

[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>.

To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale> (which may redirect to other website locations based on product family).

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity.
Regal Rexnord, Rexnord, PT Select, Rex and Link-Belt are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
© 2018, 2022 Regal Rexnord Corporation, All Rights Reserved. MCB22091E • Form# BR1-013E

 **RegalRexnord**