

Why Choose Falk™ V-Class™ Gear Drives?

MORE TORQUE CAPACITY HANDLES THE HEAVIEST LOADS


Heavy-duty ductile iron housing withstands shock loads. Optimized bevel and helical tooth forms deliver smooth torque transmission by ensuring full contact under loads.

HORIZONTALLY SPLIT HOUSING

The housing allows easy disassembly/assembly for maintenance of bearings and gearing without removing the reducer from its location.

RELIABLE COMPONENTS FOR LONG-TERM OPERATION

Magnum seals have an exclusive no-leak design with a purgeable grease chamber, and a contact seal that eliminates oil leaks while keeping dirt out.



COOLING FINS REDUCE OIL TEMPERATURE

Proprietary oil feed passages in the housing improve lubrication and provide optimal cooling.

EASY INTERCHANGE

Removable feet allow drop-in replacement for current product lines and easily adapt for replacement of competitor gear units.

INDUSTRIES SERVED:


- Mining
- Forestry
- Aggregate
- Food & Grain
- Cement
- Primary Metals
- Power Generation



Why Choose Falk™ V-Class™ Gear Drives?

FALK V-CLASS GEAR DRIVES

- 29 unit sizes, up to 3M lb-in (340 kNm) torque
- Parallel shaft (VP): single, double and triple reduction
- Right angle (VR): double and triple reduction
- Flexible mounting options: swing base, alignment-free, baseplate, top motor mount, motor bracket and integrated C-face
- Solid or hollow low speed shafts available
- Internal backstop
- Shaft fan, electric fan or DuraPlate cooling available
- Low-speed MCF flange coupling
- Three-year, heavy-duty warranty



FALK™

Regal Rexnord

Contact us: [regalrexnord.com/contact](https://www.regalrexnord.com/contact)

[regalrexnord.com](https://www.regalrexnord.com)

The proper selection and application of products and components, including assuring that the product is safe for its intended use, are the responsibility of the customer. To view our Application Considerations, please visit <https://www.regalrexnord.com/Application-Considerations>.

To view our Standard Terms and Conditions of Sale, please visit <https://www.regalrexnord.com/Terms-and-Conditions-of-Sale>

"Regal Rexnord" is not indicative of legal entity. Refer to product purchase documentation for the applicable legal entity. Regal Rexnord, Falk and V-Class are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

© 2011, 2025 Regal Rexnord Corporation, All Rights Reserved. MCF-GR5-006-FK-EN-US 12/25

RegalRexnord™